

Order code	Manufacturer code	Description
01-1286	n/a	PVC WIRE UL1007 22 AWG RED 305M REEL RC

	Page 1 of 5
The enclosed information is believed to be correct, Information may change 'without notice' due to product improvement. Users should ensure that the product is suitable for their use. E. & O. E.	Revision A 04/07/2003

ALPHA WIRE COMPANY TEL: 1-908-925-8000

Select Your Search



# Alpha Wire Company

- Home
- Master Catalog Online
- Distributor Resources
- Product Discovery Center
- Technical Resources
- New and Featured Products
- Corporate
- International



**HOOK-UP WIRE**  
**PVC INSULATION**  
 UL 1007/1569, CSA TR-64  
 80°C/105°C  
 RoHS COMPLIANT  
 300 VOLT

### CHARACTERISTICS

#### Operating Temperature:

- -40°C to 105°C - UL AWM 1569
- -40°C to 90°C - CSA TR-64
- -40°C to 80°C - UL AWM 1007

#### Voltage Rating:

- 300 Volt

#### Product Description:

- Conductor: Stranded or Solid Tinned Copper
- Insulation : Color-Coded PVC

### SPECIFICATIONS

- UL AWM Styles 1007 and 1569
- CSA TR-64
- RoHS Compliant

### AVAILABILITY

- 100 ft (30,5m), 1000 ft (305m) put-ups



Underwriters Laboratories Inc. Underwriters Laboratories Inc.



**Passes**  
**UL VW-1 Flame Test**



Canadian Standards Association



Alpha Part No.	Conduc AWG
<a href="#">3047</a>	30
<a href="#">3048</a>	28
<a href="#">3049</a>	26
<a href="#">3050</a>	24
<a href="#">3051</a>	22
<a href="#">3053</a>	20
<a href="#">3055</a>	18
<a href="#">3057</a>	16

\*See Color Code Below

### SOLID CONDUCTOR

Alpha Part No.	Conduc AWG
<a href="#">3050/1</a>	24
<a href="#">3051/1</a>	22
<a href="#">3053/1</a>	20
<a href="#">3055/1</a>	18
<a href="#">3057/1</a>	16

\*See Color Code Below



Alpha Part No.	Conduc AWG
<a href="#">3250</a>	24
<a href="#">3251</a>	22
<a href="#">3252</a>	20
<a href="#">3253</a>	18
<a href="#">3254</a>	16

\*See Color Code Below

### SEMI RIGID PVC INSULATION

UL 1061, CSA AWM I A/B [FT1](#)  
 80°C  
 RoHS COMPLIANT  
 300 VOLT

### CHARACTERISTICS

**Operating Temperature:**

- -10°C to 80°C

**Voltage Rating:**

- 300 Volt

**Product Description:**

- Conductor: Stranded [Tinned Copper](#)
- Insulation : Color-Coded, Semi Rigid PVC

1-White    4-Green    7-Brown  
 2-Black    5-Yellow    8-Orange  
 3-Red      6-Blue      9-Gray

**SPECIFICATIONS**

- UL AWM Style 1061
- CSA AWM I A/B [FT1](#)
- RoHS Compliant

**AVAILABILITY**

- 100 ft (30,5m), 1000 ft (305m) put-ups



Email: [info@alphawire.com](mailto:info@alphawire.com)

Toll Free: 1-800-52 ALPHA | Telephone: 908-925-8000 | Fax: 908-925-6923

Europe/UK Telephone: +44 (0) 800 288 8809 | Europe/UK Fax: +44 (0) 1932 77

**Master Catalog Page**

← 166 →



Copyright © 2006 Alpha Wire Company ALL RIGHTS

Use of this Web Site indicates you accept the [Terms](#) listed in the [Legal Information and Terms Of Use](#)



