



A 4mm plug which can be mounted to printed circuit boards or chassis which mates directly to 4mm sockets.

Overall length 34mm, maximum panel thickness 5.5mm, supplied fitted with two M3 nuts, panel cut-out 4mm.

Supplied in pack of 100.

Specification	
Electrical	
Maximum current	36A
Voltage	<30VAC <60VDC
Mechanical	
Contacts	Nickel plated brass
Contact resistance	<5mΩ
Temperature range	-20°C to 80°C
Thread size	M3
Thread length	12mm
Nuts	M3 (x2)