



LITHIUM / MANGANESE DIOXIDE BUTTON CELL

Model	Nominal Voltage (V)	Nominal Capacity (mAh)	Standard Discharge Current (mA)	Max. Discharge Current		Dimensions		Weight (g)
				Continuous (mA)	Pulse (mA)	Dia (mm)	Ht (mm)	
CR1216	3	28	0.05	0.2	5	12.5	1.6	0.6
CR1220	3	35	0.05	0.2	5	12.5	2.0	0.8
CR1225	3	50	0.05	0.2	5	12.5	2.5	0.9
CR1616	3	55	0.10	0.3	8	16.0	1.6	1.1
CR1620	3	70	0.10	0.3	8	16.0	2.0	1.3
CR2016	3	75	0.10	0.3	10	20.0	1.6	1.7
CR2025	3	150	0.20	0.5	15	20.0	2.5	2.7
CR2032	3	210	0.20	0.5	15	20.0	3.2	3.2
CR2320	3	150	0.20	0.5	15	23.0	2.0	3.0
CR2325	3	185	0.20	0.5	15	23.0	2.5	3.2
CR2330	3	255	0.20	0.5	15	23.0	3.0	3.8
CR2430	3	270	0.20	1.0	15	24.5	3.0	4.0
CR2450	3	500	0.20	1.0	15	24.5	5.0	6.2
CR2477	3	900	0.20	0.5	10	24.5	7.7	10.0