



## PS Range

(5yr Design Life in Float Service at 20°C)

### Dimensions (mm)




### Standard terminal (mm)



### Physical Specification

Nominal Voltage		12V
Nominal Capacity (20HR)		12.0 AH
Dimension	Length	151 ± 2 mm
	Width	98 ± 2 mm
	Container Height	95 ± 2 mm
	Total Height (with terminal)	101 ± 2 mm
Weight		Approx 3.60kg
Standard Terminal		F1

## PS-12120 12V 12AH



### Discharge Characteristics (25°C, 77°F)

Rated Capacity	20hRate(1.80V/cell)	12.00AH	Cycle	Initial Charging Current Less than 3.0A Voltage 14.40V ~ 15.0V at 25°C (77°F)
	10hRate(1.80V/cell)	11.20AH		
Capacity Affected by Temperature	5hRate(1.75V/cell)	10.20AH	Constant Voltage Charge	Standby Recommended Charge Current less than 3.0A Voltage 13.5V ~ 13.8V at 25°C (77°F)
	3hRate(1.75V/cell)	9.18AH		
	1hRate(1.60V/cell)	7.54AH		
	40°C (104°F)	103%		
	25°C (77°F)	100%		
	0°C (32°F)	86%		

### Internal Resistance mΩ

14.0 mΩ

### Constant Current Discharge (Amperes) at 25°C (77°F)

F.V/Time	5min	10min	15min	20min	30min	45min	1h	2h	3h	4h	5h	6h	8h	10h	20h
1.85V/cell	22.9	17.5	14.5	12.6	9.72	7.16	6.03	3.57	2.79	2.27	1.85	1.61	1.30	1.08	0.594
1.80V/cell	30.7	22.4	17.6	14.9	11.5	8.33	6.76	3.90	3.00	2.42	1.99	1.72	1.37	1.12	0.600
1.75V/cell	34.6	24.6	19.2	16.0	11.9	8.64	7.07	4.04	3.06	2.48	2.04	1.77	1.40	1.15	0.606
1.70V/cell	38.1	26.9	20.5	16.8	12.4	8.99	7.29	4.14	3.15	2.54	2.09	1.81	1.42	1.17	0.617
1.65V/cell	42.0	29.0	21.8	17.8	13.1	9.21	7.46	4.20	3.28	2.63	2.15	1.85	1.44	1.19	0.625
1.60V/cell	46.3	31.5	23.3	19.0	13.8	9.60	7.54	4.38	3.38	2.71	2.22	1.89	1.45	1.21	0.629

### Constant Power Discharge (Watts/cell) at 25°C (77°F)

F.V/Time	5min	10min	15min	20min	30min	45min	1h	2h	3h	4h	5h	6h	8h	10h	20h
1.85V/cell	41.8	32.4	27.1	23.7	18.5	13.8	11.6	6.93	5.44	4.44	3.63	3.16	2.56	2.14	1.18
1.80V/cell	55.5	40.9	32.3	27.6	21.5	15.9	13.0	7.51	5.82	4.71	3.88	3.37	2.71	2.21	1.19
1.75V/cell	61.2	44.3	34.9	29.4	22.2	16.3	13.5	7.76	5.91	4.80	3.97	3.46	2.75	2.26	1.20
1.70V/cell	65.6	47.1	36.7	30.7	22.9	16.9	13.9	7.94	6.06	4.92	4.06	3.52	2.78	2.31	1.22
1.65V/cell	71.3	50.4	38.7	32.3	24.0	17.2	14.1	8.01	6.29	5.07	4.16	3.59	2.82	2.35	1.23
1.60V/cell	76.8	53.5	40.8	34.1	25.2	17.8	14.2	8.31	6.45	5.21	4.28	3.65	2.84	2.37	1.24



Power-Sonic Europe Limited  
 3 Buckingham Square, Wickford, Essex, SS11 8YQ  
 Tel: +44 (0)1268 560686 Fax: +44 (0)1268 560902  
 sales@power-sonic.co.uk  
 www.power-sonic.co.uk