



### Specifications

Current rating: 15A AC,DC  
 Voltage rating: 600V AC,DC  
 Temperature range: -25°C to +85°C  
 Contact resistance: 3.5mΩ max.  
 Insulation resistance: 1000MΩ min.  
 Withstanding voltage: 5000V AC/minute  
 Material: Nylon 66, UL94V-0  
 Colour: Natural (white)

Part No.	Poles	Dimensions	
		A	B
<b>22-4230</b>	2	6.35	13.97
<b>22-4253</b>	15	25.40	33.02

