


P1,P2:	M-Y222E
	M-222E
P3:	M-426E

Customer No.: NO.43



	P1	P2	P1	P2	
BROWN	1	1	14	14	BROWN/BLACK
RED	2	2	15	15	RED/BLACK
ORANGE	3	3	16	16	ORANGE/BLACK
PINK	4	4	17	17	PINK/BLACK
YELLOW	5	5	18	18	YELLOW/BLACK
GREEN	6	6	19	19	GREEN/BLACK
LIGHT GREEN	7	7	20	20	LIGHT GREEN/BLACK
BLUE	8	8	21	21	BLUE/BLACK
LIGHT BLUE	9	9	22	22	LIGHT BLUE/BLACK
PURPLE	10	10	23	23	PURPLE/BLACK
GREY	11	11	24	24	GREY/BLACK
WHITE	12	12	25	25	WHITE/BLACK
BLACK	13	13	SHIELD	SHIELD	

NOTE: All relevant materials are complied with RoHS directive .

No.	DESCRIPTION		Q'TY	Supplier
5	BLACK PVC TUBE ϕ 3.0*30mm	H7A001-0304K09	2	M304
	ALUMINUM FOIL 33*110mm	A6MA05-0579	2	M579
	MOLDED PE COLOR TRANSPARENT	A5BA02-0280		M280
	MOLDED PVC BEIGE	H1BF01-0304B01		M304
4	NON-UL 25C 30AWG, ALUM-MYLAR FOIL SHIELDING WITH DRAIN WIRE, OD 7.0mm, JACKET BEIGE	H5BN07-0304B01	L-20mm	M304
3	MOLDED THUMBSCREW #4-40, LENGTH 46.5mm, BEIGE	A6AA30-0095	4	M95
2	DB25 FEMALE, GOLD FLASH ON CONTACTS, BLUE INSULATOR	A1AE03-0108	1	M108
1	DB25 MALE, GOLD FLASH ON CONTACTS, BLUE INSULATOR	A1AE14-0108	1	M108
APPROVED				
CHECKED				
DRAWING				
DATE	18/FEB/13	ITEM NO.		

Cable Length Unless Other Spec.
Tolerances:
0 ~200mm ±10mm
201~1000mm ±20mm
1001 ~1500mm ±25mm
1501~2100mm ±30mm
2100mm↑ ±40mm

CHECKED

