PREPARED BY JUN HEE, LEE BEGIN DATE: NOV 01,2008

## **ANNOUNCED SPECIFICATION OF** UPDATE: 2009.02.20 **HS-805MG METAL GEAR MEGA SCALE SERVO**

1.TECHNICAL VALUE

CONTROL SYSTEM OPERATING VOLTAGE RANGE

OPERATING TEMPERATURE RANGE

TEST VOLTAGE

OPERATING SPEED STALL TORQUE STANDING TORQUE

IDLE CURRENT RUNNING CURRENT STALL CURRENT DEAD BAND WIDTH

OPERATING TRAVEL

DIRECTION MOTOR TYPE

POTENTIOMETER TYPE

AMPLIFIER TYPE DIMENSIONS

WEIGHT

BALL BEARING

GEAR MATERIAL HORN GEAR SPLINE

CONNECTOR WIRE STRAND COUNTER : 60EA

CONNECTOR WIRE GAUGE

: +PULSE WIDTH CONTROL 1500usec NEUTRAL

:4.8V TO 6.0V

 $:-20^{\circ}C TO +60^{\circ}C(-4^{\circ}F TO +140^{\circ}F)$ 

AT 6.0V : AT 4.8V

:0.19sec/60° AT NO LOAD 0.14sec/60° AT NO LOAD :19.8kg.cm(274.97oz.in) 24.7kg.cm(343.01oz.in)

:8ma at stopped 10mA AT STOPPED

520mA/NO LOAD RUNNING :400mA/NO LOAD RUNNING

6,000mA : 4,800mA : 5usec 5usec :40±5°/ONE SIDE PULSE TRAVELING 400usec :CLOCK WISE/PULSE TRAVELING 1500 TO 1900usec

:CORED CARBON BRUSH

:6 SLIDER/500K CYCLE LONG LIFE/INDIRECT DRIVE


:HT7003 ANALOG AMPLIFER WITH LARGE CAPACITY TRANSISTER DRIVE


:66x30x57.6mm(2.6x1.18x2.27in)

:197g(6.95oz) :DUAL/MR148

:1 RESIN & 4 ALL METAL :13 SEGMENTS/ø7.7 : MEGA/Q-IA,Q-OA,Q-XA
CONNECTOR WIRE LENGTH : 300mm/11 81: \(\) (700) :300mm(11.81in)/TWISTED

: 22AWG





2.FEATURES DURABLE METAL GEARS WITH DUAL BALL BEARING WATER & DUST RESISTANCE

3.APPLICATIONS QUARTER SCALE MODELS

## HITEC RCD KOREA INC.