

**Notes:**

Poles: 3P

Rated voltage/current: 250V/10A Temperature range: -40°C to +105°C

Max. soldering: +250°C for 5 sec. Withstanding voltage: AC1500V/min.

Insulation resistance: 500MΩ/1000V Contact resistance: 20mΩ

Wire range: 22 to 14AWG

Torque: 0.5N·m (4.5lb. in) Undimensioned tolerances:



Pitch range in mm			Nominal dimension range in mm				
6	Over 6 upto 10	Over 10 to 24	6	Over 6 to 30	Over 30 to 90	Over 90 to 200	Over 200 to 480
±0.10	±0.15	±0.25	±0.1	±0.2	±0.3	±0.5	±0.47

No.	Description	Qty	Material	Plating
1	Base	1	PA66	IL94V-0
2	Hand	1	PA66	IL94V-0
3	Holder	1	PA66	IL94V-0
4	Current carrier	XX-2	Alloy	Ni-plated
5	Brass cage	2	Brass	Ni-plated
6	Left-clamp	1	Phosphor bronze	Ni-plated
7	Right-clamp	1	Phosphor bronze	Ni-plated
8	Screw	2XX	Steel	Cr <sup>3+</sup> + Zn
9	Clamp	2	Phosphor bronze	Ni-plated
10	Current carrier	1	Alloy	Ni-plated

