

Specifications:

- 1.0 Contact resistance: 30mΩ max.
- 1.1 Insulation resistance: 1000MΩ min. at DC 500V
- 1.2 Current rating: 1.5A
- 1.3 Voltage rating: 30V AC/DC
- 1.4 Dielectric strength: AC 500V for 1 minute

Materials:

- 2.0 Housing: PBT +30% Glass fibre (UL 94-0)
- 2.1 Contact: Copper alloy
- 2.2 Shell: Copper alloy

