



Rapid Part Number: 28-4303
Europa Part Number: LB633P
 Specifications and dimensions



- Boxed isolator 3 pole
- ABS plastic enclosure with padlockable handle

Specifications	
Height	175mm
Width	125mm
Depth	90mm
Depth including switch	134mm
Degree of protection	IP65
Rated operational current Ie AC21A	63A
Rated operational current Ie AC22A	40A
Rated operational voltage Ue IEC & EN	690V
Rated operational power AC23A 380-440V	30kW
Rated operational power AC3 440V	18.5kW
Maximum gL fuse size IEC	63A
Rated fused short circuit capacity IEC	30kA
Knockout size	25mm
Normal operating temperature	-25°C to +40°C
Maximum cable capacity	10mm ²
Recommended tightening torque	2Nm
Number of possible auxilliary contacts	1
Related products	
Main pole contact	LB263MAINPOLE
Neutral contact (early make/late break)	LB263AUXEM
Volt free contact 1NO + 1NC	LBAC16RM
Volt free contact 2NO	LBAC16RM2NO

ⓘ ALL PRODUCTS, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE.

Information provided in data sheets and/or specifications may vary from actual results in different applications and performance may vary over time. **All products must be installed according to manufacturers instructions.**

Europa House, Airport Way, Luton, Beds, LU2 9NH Tel: 01582 692 440 / Fax: 01582 692 450 e-mail: sales@europacomponents.com
 website: <http://www.europacomponents.com>