



Rapid Part Number: **28-4312**

Europa Part Number: **LB1253PSN**

Specifications and dimensions



- Boxed isolator 3 pole + switched neutral
- ABS plastic enclosure with padlockable handle

Specifications	
Height	270mm
Width	215mm
Depth	122mm
Depth including switch	182mm
Degree of protection	IP65
Rated operational current Ie AC21A	125A
Rated operational current Ie AC22A	125A
Rated operational voltage Ue IEC & EN	690V
Rated operational power AC23A 380-440V	75kW
Rated operational power AC3 440V	55kW
Maximum gL fuse size IEC	125A
Rated fused short circuit capacity IEC	30kA
Knockout size	25mm
Normal operating temperature	-25°C to +40°C
Maximum cable capacity	50mm ²
Recommended tightening torque	2.5Nm
Number of possible auxilliary contacts	None

ⓘ **ALL PRODUCTS, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE.**

Information provided in data sheets and/or specifications may vary from actual results in different applications and performance may vary over time. **All products must be installed according to manufacturers instructions.**

Europa House, Airport Way, Luton, Beds, LU2 9NH Tel: 01582 692 440 / Fax: 01582 692 450 e-mail: sales@europacomponents.com
 website: <http://www.europacomponents.com>