



Rapid Part Number: **28-4317**

Europa Part Number: **LB1004PSTB**

Specifications and dimensions

- Boxed isolator 4 pole
- Metal enclosure with padlockable handle
- Epoxy coated steel construction



Specifications	
Height	270mm
Width	215mm
Depth	125mm
Depth including switch	185mm
Degree of protection	IP54
Colour of base	RAL7043
Colour of Lid	RAL7032
Rated operational current Ie AC21A	100A
Rated operational current Ie AC22A	100A
Rated operational voltage Ue IEC & EN	690V
Rated operational power AC23A 380-440V	55kW
Rated operational power AC3 440V	45kW
Maximum gL fuse size IEC	125A
Rated fused short circuit capacity IEC	30kA
Normal operating temperature	-25°C to +40°C
Maximum cable capacity	50mm ²
Recommended tightening torque	2.5Nm
Number of possible auxilliary contacts	1
Related products	
Neutral contact (early make/late break)	LB280AUXEM
Volt free contact 1NO + 1NC	LBAC125RM
Volt free contact 2NO	LBAC125RM2NO

ⓘ ALL PRODUCTS, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE.

Information provided in data sheets and/or specifications may vary from actual results in different applications and performance may vary over time. **All products must be installed according to manufacturers instructions.**

Europa House, Airport Way, Luton, Beds, LU2 9NH Tel: 01582 692 440 / Fax: 01582 692 450 e-mail: sales@europacomponents.com
website: <http://www.europacomponents.com>