



Rapid Part Number: **28-4347**
 Europa Part Number: **LB258P**
 Specifications and dimensions

- Boxed isolator 8 pole
- ABS plastic enclosure with lockable handle



Specifications	
Height	280mm
Width	190mm
Depth	130mm
Depth including switch	190mm
Degree of protection	IP65
Rated operational current Ie AC21A	32A
Rated operational current Ie AC22A	25A
Rated operational voltage Ue IEC & EN	690V
Rated operational power AC23A 380-440V	15kW
Rated operational power AC3 440V	11kW
Maximum gL fuse size IEC	32A
Rated fused short circuit capacity IEC	30kA
Normal operating temperature	-25°C to +40°C
Maximum cable capacity	10mm ²
Recommended tightening torque	1.7Nm
Number of possible auxilliary contacts	2
Related products	
Main pole contact	LB263MAINPOLE
Volt free contact 1NO + 1NC	LBAC16RM
Volt free contact 2NO	LBAC16RM2NO

ⓘ **ALL PRODUCTS, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE.**

Information provided in data sheets and/or specifications may vary from actual results in different applications and performance may vary over time. **All products must be installed according to manufacturers instructions.**

Europa House, Airport Way, Luton, Beds, LU2 9NH Tel: 01582 692 440 / Fax: 01582 692 450 e-mail: sales@europacomponents.com
 website: <http://www.europacomponents.com>