



Rapid Part Number: **28-4356**

Europa Part Number: **LB263MAINPOLE**

Specifications and dimensions



- Main Pole Auxilliary Contact
- NO Configuration
- Suitable for LB Boxed Isolators up to 63A and LBDI Door Interlock Isolators up to 63A

Dimensions:	
Height	72mm
Width	18mm
Depth	39mm
Features	
Rated operational voltage Ue IEC &EN	690V
Rated operational voltage Ue UL	600V
Rated impulse withstand voltage Uimp	6kV
Rated uninterrupted current Iu	63A
Rated operational current Ie AC22A	63A
Rated operational current Ie AC21A	80A
Rated operational current Ie AC1	80A
Rated operational power AC23A (50/60Hz) 230V	30kW
Rated operational power AC23A (50/60Hz) 415V	37kW
Rated operational power AC23A (50/60Hz) 690V	45kW
Rated operational power AC3 (50/60Hz) 230V	22kW
Rated operational power AC3 (50/60Hz) 415V	22kW
Rated operational power AC3 (50/60Hz) 690V	30kW
UL power rating 3 phase DOL 110V	7.5hp
UL power rating 3 phase DOL 230V	15hp
UL power rating 3 phase DOL 480V	25hp
UL power rating 3 phase DOL 600V	30hp
UL power rating 1 phase DOL 110V	3hp
UL power rating 1 phase DOL 230V	7.5hp
UL short circuit fuse rating class J	70A
UL rated fused short circuit current	10kA
IEC short circuit capacity max fuse size GI	63A
IEC rated fused short circuit current	30kA
Maximum terminal capacity	25mm ²
Recommended tightening torque terminal	2.0 Nm
Recommended tightening torque fixing screw	0.3Nm

ⓘ ALL PRODUCTS, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE.

Information provided in data sheets and/or specifications may vary from actual results in different applications and performance may vary over time. **All products must be installed according to manufacturers instructions.**

Europa House, Airport Way, Luton, Beds, LU2 9NH Tel: 01582 692 440 / Fax: 01582 692 450 e-mail: sales@europacomponents.com
website: <http://www.europacomponents.com>