



Rapid Part Number: 28-4359 **Europa Part Number: LBAC125RM**

Specifications and dimensions

- Volt free contact auxiliary block
- 1NC and 1NO configuration
- NO contact is early make/late break





1NC & 1NO



Features	
Height	72mm
Width	21mm
Depth	47mm
Standard	IEC & EN 60947-3
Rated operational voltage Ue IEC &EN	500V
Rated operational current le AC15 240V	6A
Rated operational current le AC15 415V	4A
Maximum terminal capacity	1.5mm ²
Recommended tightening torque terminal	0.8Nm
Recommended tightening torque fixing screws	0.3Nm
Suitable for	
LB boxed isolators 80A to 125A	

(1) ALL PRODUCTS, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE.

Information provided in data sheets and/or specifications may vary from actual results in different applications and performance may vary over time. All products must be installed according to manufacturers instructions.

Europa House, Airport Way, Luton, Beds, LU2 9NH Tel: 01582 692 440 / Fax: 01582 692 450 e-mail: sales@europacomponents.com website: http://www.europacomponents.com

Page 1 of 1

LBDI door interlock isolators 80A to 125A