



Rapid Part Number: 28-4573 **Europa Part Number: TA1-DN20** 

Specifications and dimensions







•	Auxiliary	contact	block	for	contactors
---	-----------	---------	-------	-----	------------

Top mounting

Dimensions				
Height	53mm			
Width	27mm			
Depth	46mm			
Weight	0.039Kg			
Features				
Standard	IEC 60947-1			
Number and type of contacts	2 NO			
Rated thermal current Ith	10A			
Minimum switching voltage	17V			
Minimum switching amperage	5mA			
Ingress Protection Rating	IP20			
Ambient Temperature Operating	-40 to +70°C			
Maximum rated operational voltage	690V			
Terminal capacity	2.5mm <sup>2</sup>			
Tightening torque	1.85Nm			

## (1) ALL PRODUCTS, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE.

Information provided in data sheets and/or specifications may vary from actual results in different applications and performance may vary over time. All products must be installed according to manufacturers instructions.

Europa House, Airport Way, Luton, Beds, LU2 9NH Tel: 01582 692 440 / Fax: 01582 692 450 e-mail: sales@europacomponents.com website: http://www.europacomponents.com

Page 1 of 1