



Rapid Part Number: 28-4602

Europa Part Number: TC1-D40004B7

Specifications and dimensions

- 4 pole contactor with AC coil
- Din rail or surface mount
- 4 normally open main poles



1g 3g 5g
O
O TC1D4011
€ € Q 211 412 611

Features		
Height	127mm	
Width	85mm	
Depth	114mm	
Weight	1.15Kg	
Maximum standard power rating 415V AC3	22kW	
Maximum switching current AC3	40A	
Maximum switching current AC1	60A	
Maximum rated voltage	690V	
Standard	EN 60947-4-1	
Mounting position from vertical plane	± 30°	
Maximum operating rate cycles per hour	3600	
Coil voltage	24V AC 50/60 Hz	
Coil consumption inrush	245VA	
Coil consumption sealed	26VA	
Ambient temperature storage	,-50°C to +80°C	
Ambient temperature operation	,-5°C to +55°C	
Mechanical life - number of operations	6 x 106	
Maximum cable size for power contacts	25mm²	
Related Products		
Plastic enclosure	PB65C	
Metal enclosure	STB252515	
Thermal overload range	TR2	
Front mount auxilliary block range	TA1	
Side mount auxilliary block range	TA8	
Front mount timer range	TA2/TA3	
Mechanical interlock	LA9-D50978	
Spare coil	TX1D6B7	

## (1) ALL PRODUCTS, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE.

Information provided in data sheets and/or specifications may vary from actual results in different applications and performance may vary over time. All products must be installed according to manufacturers instructions.

Europa House, Airport Way, Luton, Beds, LU2 9NH Tel: 01582 692 440 / Fax: 01582 692 450 e-mail: sales@europacomponents.com website: http://www.europacomponents.com

Page 1 of 1

**EPC**2085-001RA