Europa T	=Rapid
-----------------	---------------

Rapid Part Number: 28-4608 Europa Part Number: TR2-D09301

Specifications and dimensions

- Class 10 thermal overload relay for TC1 contactor range
- Connection by screw clamp direct to contactor or remote by mounting block
- With 1 NO and 1 NC auxilliary contacts

Dimensions		
Height	92mm	
Width	44mm	
Depth	47mm	
Weight	0.183 Kg	
Features		
Ingress Protection Rating	IP20	
Ambient Temperature Storage	-60 to +70°C	
Ambient Temperature Operating	-40 to +70°C	
Maximum rated operational voltage	600V	
Maximum contactor size	D38	
Setting range	0.1 to 0.16 A	
Terminal capacity flexible cable with ferrule	4mm ²	
Tightening torque	1.7 Nm	
Tripping Threshold	1.14 ±0.06 In	
Auxilliary Contact		
Thermal amperage	5A	
Tightening torque	1.85 Nm	
Terminal capacity flexible cable with ferrule	2.5mm ²	
Related Products		
Overload mounting plate	TA7-D0964	

(i) ALL PRODUCTS, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE.

Information provided in data sheets and/or specifications may vary from actual results in different applications and performance may vary over time. All products must be installed according to manufacturers instructions.

Europa House, Airport Way, Luton, Beds, LU2 9NH Tel: 01582 692 440 / Fax: 01582 692 450 e-mail: sales@europacomponents.com website: http://www.europacomponents.com



RoHS Compliant