



Sample image

**Order symbol:** FP 10674

**Product nbr:** 5510674

**Description:** Mounting foot kit (2 pcs)  
incl. screws

**Remarks:** (MNX 300 requires 2 sets) Not  
for CM 30/25

**Including:**

**EAN:** 6418074033079

**EI. number:**

- Finland: 3424980
- Denmark:
- Sweden: 2537245

Dimensions:	Length	Width	Height
mm:		0	0
inch:		0	0

**Materials:**

Material:

Base colour:

Cover colour:

Gasket material:

**Rating:**

Ingress protection (EN 60529):

Impact Resistance (EN 62262):

Electrical insulation: Not insulated

Halogen free (DIN/VDE 0472, Part 815): 0

UV resistance: -

Flammability Rating:

Glow Wire Test (IEC 695-2-1) °C:

NEMA Class

**Temperatures:**

Temperature °C (short term):

Temperature °C (continuous):

Temperature °F (short term):

Temperature °F (continuous):

**Certificates:**