



Sample image

Order symbol: MIV 125

Product nbr: 5514077

Description: Back Panel (Galvanized steel).
for enclosures:

Remarks: 130x130x35-130x130x125

Including:

EAN: 6418074039491

El. number:

- Finland: 3424961
- Denmark: 8212000968
- Sweden: 2537214

Dimensions:	Height	Width	Depth
mm:	98	98	1

Rating:
Ingress protection (EN 60529):

inch:	3.86	3.86	0.04
-------	------	------	------

Materials:

Material:

Base colour:

Cover colour:

Gasket material:

Temperatures:

Temperature °C (short term):

Temperature °C (continuous):

Temperature °F (short term):

Temperature °F (continuous):

Impact Resistance (EN 62262):

Electrical insulation: Not insulated

Halogen free (DIN/VDE 0472, Part 815): 0

UV resistance: -

Flammability Rating:

Glow Wire Test (IEC 695-2-1) °C: C

NEMA Class

Certificates: