



Sample image

Order symbol: MIV 200

Product nbr: 5514080

Description: Back Panel (Galvanized steel).
for enclosures:

Remarks: 255x180x63-255x180x175

Including:

EAN: 6418074039521

El. number:

- Finland: 3424964
- Denmark: B212000997
- Sweden: 2537223

Dimensions:	Height	Width	Depth
mm:	223	148	1

Rating:
Ingress protection (EN 60529):

inch:	8.78	5.83	0.04
-------	------	------	------

Materials:

Material:

Base colour:

Cover colour:

Gasket material:

Temperatures:

Temperature °C (short term):

Temperature °C (continuous):

Temperature °F (short term):

Temperature °F (continuous):

Impact Resistance (EN 62262):

Electrical insulation: Not insulated

Halogen free (DIN/VDE 0472, Part 815): 0

UV resistance: -

Flammability Rating:

Glow Wire Test (IEC 695-2-1) °C: C

NEMA Class

Certificates: