

# NEO MPS 3222



Sample image

**Order symbol:** NEO MPS 3222

**Product nbr:** 4850060

**Description:** Metal mounting plate

**Remarks:**

**Including:** Metal mountingplate

**EAN:** 6418074314765

**El. number:**

- Finland: 3424421
- Denmark: 8212098129
- Sweden: 2506225

NEO MPS 3222.jpg

<b>Dimensions:</b>	<b>Height</b>	<b>Width</b>	<b>Depth</b>
mm:	275	165	1.5
inch:	10.83	6.5	0.06

#### **Materials:**

Material:	Galvanized steel
Base colour:	
Cover colour:	
Gasket material:	

#### **Temperatures:**

Temperature °C (short term)::
Temperature °C (continuous):
Temperature °F (short term):
Temperature °F (continuous):

#### **Rating:**

Ingress protection (EN 60529):	
Impact Resistance (EN 62262):	
Electrical insulation:	Not insulated
Halogen free (DIN/VDE 0472, Part 815):	1
UV resistance:	-
Flammability Rating:	
Glow Wire Test (IEC 695-2-1) °C:	C
NEMA Class	

#### **Certificates:**