

PMK ARCA 50



Sample image

Order symbol: PMK ARCA 50

Product nbr: 8120843

Description: PoleMounting kit. for pole \varnothing 100-300mm

Remarks: For sizes 400x500x210. 700x500x300

EAN: 6418074083234

El. number:

- Finland: 3424027
- Denmark: 8212095083
- Sweden: 2500211

Including:

Dimensions:	Length	Width	Height
-------------	--------	-------	--------

mm:		385	485
-----	--	-----	-----

inch:		15.16	19.09
-------	--	-------	-------

Materials:

Material:

Base colour:

Cover colour:

Gasket material:

Temperatures:

Temperature °C (short term):

Temperature °C (continuous):

Temperature °F (short term):

Temperature °F (continuous):

Rating:

Ingress protection (EN 60529):

Impact Resistance (EN 62262):

Electrical insulation: Not insulated

Halogen free (DIN/VDE 0472, Part 815): 0

UV resistance: -

Flammability Rating:

Glow Wire Test (IEC 695-2-1) °C:

NEMA Class

Certificates: