

PMK ARCA 60

FIBOX

Enclosing innovations



Sample image

Order symbol: PMK ARCA 60

Product nbr: 8120844

Description: PoleMounting kit. for pole
ø100-300mm

Remarks: For sizes 400x600x210.
800x600x300

Including:

EAN: 6418074083241

El. number:

- Finland: 3424029
- Denmark: 8212095096
- Sweden: 2500212

Dimensions:	Height	Width	Depth
mm:	585	385	35
inch:	23.03	15.16	1.38

Materials:

Material:

Base colour:

Cover colour:

Gasket material:

Rating:

Ingress protection (EN 60529):

Impact Resistance (EN 62262):

Electrical insulation: Not insulated

Halogen free (DIN/VDE 0472, Part 815): 0

UV resistance: -

Flammability Rating:

Glow Wire Test (IEC 695-2-1) °C: C

NEMA Class

Temperatures:

Temperature °C (short term):

Temperature °C (continuous):

Temperature °F (short term):

Temperature °F (continuous):

Certificates: