

Hand-Held and Remote

| Order code | Manufacturer code | Description |
|------------|-------------------|----------------------------------|
| 30-1655 | 110-407 | 182X180X90 POLYSTYRENE ENCLOSURE |
| 30-1755 | 120-407 | 182X180X90 POLYCARB.ENCLOSURE |

| | |
|--|--------------------------|
| Hand-Held and Remote | Page 1 of 2 |
| The enclosed information is believed to be correct, Information may change 'without notice' due to product improvement. Users should ensure that the product is suitable for their use. E. & O. E. | Revision A 04/07/2003 |

Polystyrene/Polycarbonate Enclosures

Specification

| Rapid Order Code | Material Used |
|------------------|--------------------------------------|
| 30-1655 | Polystyrene |
| 30-1755 | Glass-fibre reinforced Polycarbonate |

| Parameter | Material Type | |
|--------------------------------|---|---|
| | Polystyrene | Polycarbonate |
| Material Properties | Low Halogen Resistance to water, alcohol, weak acid. | Zero Halogen Resistance to water, alcohol, petrol, mineral oil, vegetable & animal fats, weak & strong acids |
| UV Resistance | - | Approved to UL 746 (sec.26) |
| Flammability | UL94V-2 | UL94V-1 |
| Continuous Working Temperature | +70°C | +115°C |
| Minimum Working Temperature | -40°C | -35°C |
| Maximum Working Temperature | +80°C | +130°C |
| Colour | Grey (RAL7035) | |
| Rating | IP66 | |

Technical Drawing

