

ARCA 604021

Order symbol: ARCA 604021
Product nbr: 8120012
Description: Cabinet, PC
Remarks: 2-point locking

EAN: 6418074079237
EI. number:
 Finland: 3423100
 Electric No. 8212091100
 Denmark:
 Electric No. Sweden: 2500118



Sample photo

Including: Cabinet base, door with PUR gasket, mounting plate, screws for mounting plate. 3mm double bit lock(s) with key. S versions with swinghandle 2-point locking system. F versions with flange opening. Door guide included.

Dimensions:				Accessories:	
	Length	Width	Height		
mm:	600	400	210	MPP ARCA 6040	Mounting plate perforated (550x350x2 mm - 26x11 mm)
inch:	23.6	15.7	8.3	MPMP ARCA 6040	Mounting plate multiperforated (550x350x2 mm - □3.6 mm)
Materials:				MPX ARCA 6040	Mounting plate (550x350 mm)
Material:	Polycarbonate			DRS ARCA 604021	DIN rail frame set
Base colour:	RAL 7035 -light grey			DRS ARCA 604030	DIN rail frame set
Cover colour:	RAL 7035 -light grey			IDS ARCA 6040	Inner door set
Gasket material:	Polyurethane			PMK ARCA 40	Pole mounting kit
Temperatures:				RCS ARCA 6040	Rain canopy set
				Rating:	
Temperature °C (short term):	-40 ... 120 °C			Ingress Protection (EN 60529): IP66	
Temperature °C (continuous):	-40 ... 80 °C			Impact Resistance (EN 62262): IK10 +35°C /IK08 -25°C	
Temperature °F (short term):	-40 ... 250 °F			Electrical insulation: Totally insulated	
Temperature °F (continuous):	-40 ... 175 °F			Halogen free (DIN/VDE 0472, Part 815): 1	
Accessories:				UV resistance: UL 508	
				Flammability Rating: UL 746C 5V	
MPS ARCA 6040	Mounting plate (550x350x2 mm)			Glow Wire Test (IEC 695-2-1) °C: 960	
Certificates:				SGS Fimko	
				Gost R	

