

M4 Stud Size 25A Red Ring Connector Pack of 100

Order code: **33-0610**

Note:

- 1. Maximum electric current:
- 2. Maximum electrical rating:
- 3. Insulation material:
- 4. Insulator colour:
- 5. Terminal material:
- 6. Wire range:
- 7. Terminal surface treatment:
- 8. Terminal thickness:

AWG	22	20	18	16
AMP	9	12	17	18

105°C 600 volts max.

Vinyl

Red

Copper

22-16 AWG (0.5-1.5mm²)

Tin plated

0.75mm

