

A

B

C

D

E

F




G

H

REV

DESCRIPTION

DATE



NOTE :

1. MAXIMUM ELECTRIC CURRENT :

A.W.G.	12	10	
AMP.	20	24	
2. MAXIMUM ELECTRICAL RATING : 75°C 600 VOLTS MAX.
3. INSULATION MATERIAL : VINYL
4. INSULATION COLOR : YELLOW
5. TERMINAL MATERIAL : BRASS
6. WIRE RANGE : 12-10 A.W.G. (4 - 6 mm²)
7. DOUBLE CRIMP : WITH COPPER SLEEVE ON BARREL
8. TERMINAL SURFACE TREATMENT : TIN PLATED
9. TERMINAL THICKNESS : 0.40 mm

Tolerance Unless
Otherwise Specified

0 > 6 mm ± 0.20	ANGLE
6 > 18 mm ± 0.30	0° REF ±
18 > 30 mm ± 0.40	° ±
30 > 75 mm ± 0.50	° ±

NAME	VINYL-INSULATED DOUBLE CRIMP BULLET DISCONNECTORS			UNIT	⊕	⊖
PART NO.	MPD5-195	MATERIAL	-----	APPROVE	[Signature]	
NUMBER	KA-95157-C	SCALE	SHEET	PAGE	CHECKED	[Signature]
DATE	2006/03/28	4/1	1-0	10F2	DRAWN	張馨尹

KST. K.S. TERMINALS INC.