



The right lighting can make all the difference to the atmosphere of a home, office or outdoor space. That's why GET has put a great deal of thought into a range of lighting luminaires that are both aesthetically pleasing and easy to install.

For indoor use, choose between mood enhancing, decorative luminaires and more functional fittings for kitchens, bathrooms and commercial spaces.

And why stay indoors on a warm summer evening, when external lighting will create the perfect al fresco environment? GET's range of outdoor lighting solutions can illuminate gardens, walkways and doorways – or offer a little extra security.

New for this edition are fire rated downlighters and T4 mini batten fluorescent fittings.

Indoor Downlighters		-141 -130
Fire rated Die cast Pressed Shower lights Die cast with floating glass Transformers Recessed wall and ceiling T4 mini batten	126-	121 122 123 122 124 125 127 129
Cabinet and undershelf lighting		130
Bathroom range	131-	
Wall and ceiling Shaver lights Shower lights		132 133 134
Decorative range	135-	139
GU10 Spotlights GU10 Flat plate Compact fluorescents G9 Spotlight Wall and Ceiling		136 137 137 138 139
Fluorescent battens & diffusers	140	141
Battens Diffusers Reflectors		141 141 141
Outdoor Amenity	142 -142-	
Drums Bulk head and bricklights Flood lighting		143 144 144
Low voltage	145-	154
Ezclick system LED decklights Tall post lights Pagoda, spotlights + postlights Decklights, spotlights + bollards Stone effect post lights 6 sided lanterns Stone effect novelty Caplights + stormlights Lanterns + halo postlights Pagoda postlights		146 147 148 148 149 150 150 151 152 153 154
Mains voltage	155-	157
Tall postlights Stainless steel posts Steel + copper lanterns Traditional + modern style lantern		156 156 156 157
Lamps	158-	164
Incandescent Halogen Energy saving Compact fluorescent T4 + T5 miniature fluorescent Energy saving lampholder		
Tochnical information	100-	105

Technical information

190-195

(G) (G) (T)

Lighting Solutions...



Fire Rated Downlighters - Page 121



Downlighters - Pages 122-123

...for domestic, commercial and industrial applications



T4 Mini Batten Luminaires - Page 129




Cabinet Lighting - Page 130



Bathroom Lighting -Pages 131-133



Batten Fittings - Pages 140-141



Amenity Lighting - Pages 142-144



Outdoor Low Voltage Lighting - Pages 145-154



Energy Saving - Page 161



Lamps - Pages 158-164





new lighting products



Fire rated downlighters

The new range of fire and acoustic rated Downlights from GET is the ideal choice for commercial or domestic installations. Supplied in fixed, tilt or shower versions, in chrome, white or stainless steel finishes and available for mains or low voltage applications.

Downlighters - Page 121

Fire rated downlighters

Maintain fire resistance of load bearing floors for up to 90 minutes. Acoustic rating to BS EN ISO 140-3:1995 and 140-6:1998.

Downlighters - Page 121





T4 mini batten luminaires

Provide ambience to any kitchen work surface with GET's new range of T4 Mini Batten Fittings. Supplied in 275mm, 400mm, 500mm and 625mm versions, all mini battens can be interconnected directly or with the supplied link cable.

Mini battens - Page 129

T4 mini batten lighting

Quality mini battens to BS EN 60598 with CE and F Mark approval.

Mini battens - Page 129







Light | Indoor lighting | Downlighters

Our versatile downlighter range can add simple, understated ambience or direct accent lighting to any domestic or commercial area. With a wide choice of lamp types and finishes as well as ceiling, wall or stair models. Our luminaires will complement any interior styling.

The low voltage and GU10 ranges found on pages 122-123 have been colour matched with a choice of seven high quality finishes to complement our Ultimate wiring accessory range (see pages 20-57).

	D	0	۷n	ligh	iter	ran	ige
--	---	---	----	------	------	-----	-----

Fire rated: GU10/Low voltage

Page 121

Die cast: GU10/Low voltage

Page 122

Pressed metal: GU10/Low voltage

Page 123

Die cast with floating glass: GU10/Low voltage

Page 124

This section also features:

Transformers: Low voltage Page 125
Wall, stair and ceiling (matt steel) LED, Low voltage, G9 Pages 126-127

Light | Indoor lighting | Downlighters Fire rated - low voltage and mains halogen



max)

max)

max)

Low voltage MR16 halogen downlighters (lamp included)







Code	Description	Qty		
Fixed GDFLLD50C GDFLLD50W GDFLLD50SS	Chrome White Stainless steel	10 10 10	Lamp: Cut-out (mm): Ceiling Depth:	MR16 (50W 72mm 100mm
Tilt GDFLLTD50C GDFLLTD50W GDFLLTD50SS	Chrome White Stainless steel	10 10 10	Lamp: Cut-out (mm): Ceiling Depth:	MR16 (50W 83mm 100mm
Shower GDFLLS50C GDFLLS50W GDFLLS50SS	Chrome White Stainless steel	10 10 10	Lamp: Cut-out (mm): Ceiling Depth:	MR16 (50W 74mm 100mm

Features:

- Max rating 50W when used with aluminised lamp (code HD50WM2582A). When used with non-aluminised lamps max rating of lamp must be 35W.
- Shower version rated to IP65 and can be installed in zones 1, 2 and 3 (see page 133).

Mains voltage GU10 halogen downlighters (lamp included)







Code	Description	Qty		
Fixed				
GDFLGD50C	Chrome	10	Lamp:	GU10 (50W max)
GDFLGD50W	White	10	Cut-out (mm):	72mm
GDFLGD50SS	Stainless steel	10	Ceiling Depth:	100mm
Tilt				
GDFLGTD50C	Chrome	10	Lamp:	GU10 (50W max)
GDFLGTD50W	White	10	Cut-out (mm):	83mm
GDFLGTD50SS	Stainless steel	10	Ceiling Depth:	100mm
Shower				
GDFLGS50C	Chrome	10	Lamp:	GU10 (50W max)
GDFLGS50W	White	10	Cut-out (mm):	74mm `
GDFLGS50SS	Stainless steel	10	Ceiling Depth:	100mm

Features

- Maintain fire resistance of load bearing floors for up to 90 minute ceilings to BS476 parts 20, 21 and 23
- Moisture resistant seals for fixed version
- Die cast construction c/w stirrup and enclosed terminal block
- · Quick fix steel clips to ensure secure fixing
- Shower version rated to IP65
- Accoustic rating to BS EN ISO 140-3: 1995 and 140-6 1998

Light | Indoor lighting | Downlighters Die cast metal – low voltage and mains halogen



Low voltage MR16 halogen downlighters (lamp required)









Code	Description	Qty
Fixed		
GDLLD50B	Polished brass	6
GDLLD50C	Polished chrome	6
GDLLD50W	White	6
GDLLD50BB	Brushed brass	6
GDLLD50CB	Brushed chrome	6
GDLLD50BN	Black nickel	6
GDLLD50PN	Pearl nickel	6
GDLLD50SS	Stainless steel	6


Tilt		
GDLLTD50B	Polished brass	6
GDLLTD50C	Polished chrome	6
GDLLTD50W	White	6
GDLLTD50BB	Brushed brass	6
GDLLTD50CB	Brushed chrome	6
GDLLTD50BN	Black nickel	6
GDLLTD50PN	Pearl nickel	6

Wall wash		
GDLLW50B	Polished brass	6
GDLLW50C	Polished chrome	6
GDLLW50W	White	6
GDLLW50BB	Brushed brass	6
GDLLW50CB	Brushed chrome	6

Shower		
GDLLS50B	Brass	1
GDLLS50C	Chrome	1
GDLLS50W	White	1
GDLLS50SS	Stainless steel	1
GDLLS50BN	Black nickel	1
GDLLS50BS	Satin brass	1
GDLLS50PN	Pearl nickel	1
GDLLS50BN GDLLS50BS	Black nickel Satin brass	1 1

Lamp: MR16 (50W max)
Cut-out (mm): 60mm
Ceiling Depth: 116mm

Diameter:	80mm



Lamp: MR16 (50W max)
Cut-out (mm): 110mm
Ceiling Depth: 105mm
Diameter: 127mm

Lamp: MR16 (50W max)
Cut-out (mm): 72.5mm
Ceiling Depth: 100mm
Diameter: 83mm
Suitable for use in Zone 1

Shower version rated to IP65

Mains voltage GU10 halogen downlighters (lamp included)



GDLGTD50PN



Code	Description	Qty
Fixed		
GDLGD50B	Polished brass	6
GDLGD50C	Polished chrome	6
GDLGD50W	White	6
GDLGD50BB	Brushed brass	6
GDLGD50CB	Brushed chrome	6
GDLGD50BN	Black nickel	6
GDLGD50PN	Pearl nickel	6

Tilt GDLGTD50B GDLGTD50C GDLGTD50W GDLGTD50BB GDLGTD50CB GDLGTD50BN GDLGTD50PN	Polished brass Polished chrome White Brushed brass Brushed chrome Black nickel Pearl nickel	666666
Shower GDLGS50B	Brass	1

0.2 2 0.1 2 0 0 1 1 1	· carrinoner	•
Shower		
GDLGS50B	Brass	1
GDLGS50C	Chrome	1
GDLGS50W	White	1
GDLGS50SS	Stainless steel	1
GDLGS50BN	Black nickel	1
GDLGS50BS	Satin brass	1
GDLGS50PN	Pearl nickel	1

Lamp:	GU10 (50W max)
Cut-out (mm):	60mm

Ceiling Depth: 116mm
Diameter: 80mm

Lamp:	GU10 (50W max)
Cut-out (mm):	65mm

Ceiling Depth: 116mm
Diameter: 80mm

Lamp:	GU10 (50W max)
Cut-out (mm):	72.5mm
Ceiling Depth:	100mm
Diameter:	83mm
Shower version	n rated to IP65


Light | Indoor lighting | Downlighters Pressed metal – low voltage and mains halogen



Low voltage MR16 downlighters (lamp required)








Code	Description	Qty		
Fixed GDLL50B GDLL50C GDLL50W GDLL50BB GDLL50CB GDLL50BN	Polished brass Polished chrome White Brushed brass Brushed chrome Black nickel	6 6 6 6	Lamp: Cut-out (mm): Ceiling Depth: Diameter:	MR16 (50W max) 65mm 116mm 80mm
Eyeball GDLLE50B GDLLE50C GDLLE50W GDLLE50BB GDLLE50CB GDLLE50BN	Polished brass Polished chrome White Brushed brass Brushed chrome Black nickel	6 6 6 6	Lamp: Cut-out (mm): Ceiling Depth: Diameter:	MR16 (50W max) 95mm 125mm 110mm
Tilt GDLLT50B GDLLT50C GDLLT50W GDLLT50BB GDLLT50CB GDLLT50BN	Polished brass Polished chrome White Brushed brass Brushed chrome Black nickel	6 6 6 6	Lamp: Cut-out (mm): Ceiling Depth: Diameter:	MR16 (50W max) 80mm 116mm 105mm

Mains voltage GU10 downlighters (lamp included)







Code	Description	Qty
Fixed		
GDLG50B	Polished brass	6
GDLG50C	Polished chrome	6
GDLG50W	White	6
GDLG50BB	Brushed brass	6
GDLG50CB	Brushed chrome	6
GDLG50BN	Black nickel	6
Eyeball		
GDLGE50B	Polished brass	6
GDLGE50C	Polished chrome	6
GDLGE50W	White	6
GDLGE50BB	Brushed brass	6
GDLGE50CB	Brushed chrome	6
GDLGE50BN	Black nickel	6
Tilt		
GDLGT50B	Polished brass	6
GDLGT50C	Polished chrome	6
GDLGT50W	White	6
GDLGT50BB	Brushed brass	6
GDLGT50CB	Brushed chrome	6
GDLGT50BN	Black nickel	6



6	Lamp:	GU10 (50W max)
6 6	Cut-out (mm):	65mm
6	Ceiling Depth:	116mm
6 6	Diameter:	80mm
6	Lamp:	GU10 (50W max)
6 6	Cut-out (mm):	95mm
6	Ceiling Depth:	125mm
6 6	Diameter:	110mm
6	Lamp:	GU10 (50W max)
6 6	Cut-out (mm):	80mm
6	Ceiling Depth:	116mm
6 6	Diameter:	105mm

Features:

- Fixed, eyeball and tilt models
- Complete with stirrup and covered terminal block, quick fit steel spring clips and a lamp retaining clip
- For use with max 50W MR16 dichroic lamp (not included) or mains voltage GU10 lamp (included)
- Individually boxed
- Dichroic lamps reflect the heat backwards to provide a cool beam while GU10 lamps reflect heat forwards
- Suitable for commercial and domestic applications

A range of pressed downlighters that are suitable for both domestic and commercial applications. The range is available in six finishes to suit a variety of interior styles and can be easily installed.

Light | Indoor lighting | Downlighters Die cast with floating glass - low voltage and GU10



Floating glass (lamp not included)



Code	Colour	Description	Qty
GDLLG50B	Brass	Downlighter with floating glass	1
GDLLG50C	Chrome	Downlighter with floating glass	1
GDLLG50W	White	Downlighter with floating glass	1

Lamp:	MR16 (50W max)
Cut-out (mm):	65mm
Ceiling Depth:	116mm
Dimensions:	Luminaire 78mm

Luminaire 78mm x 78mm Floating glass 85mm x 85mm



Code	Colour	Description	Qty
GDLGG50B	Brass	Downlighter with floating glass	1
GDLGG50C	Chrome	Downlighter with floating glass	1
GDLGG50W	White	Downlighter with floating glass	1

Lamp: GU10 (50W max) Cut-out (mm): 65mm Ceiling Depth: 116mm

Dimensions: Luminaire 78mm x 78mm Floating glass 85mm x 85mm







Floating glass luminaires create a pleasant diffuse effect with some upward light component.

- Square downlighter with etched glass to diffuse the light from the lamp evenly
- Complete with stirrup and covered terminal block, quick fit steel spring clips and a lamp retaining clip
- For use with max 50W MR16 dichroic lamp (not included) or mains voltage GU10 lamp (included)
- Dichroic lamps reflect heat backwards to provide a cool beam while GU10 lamps reflect heat forwards
- Suitable for commercial and domestic applications

Light | Indoor lighting Downlighter transformers



Transformers - Performer



Code	Description	Qty	
GTRE65	65VA electronic dimmable transformer	1	,
GTRE105	105VA electronic dimmable transformer	1	,
GTRE150	150VA electronic dimmable transformer	1	,
GTRE200	200VA electronic dimmable		

transformer

124(W) x 40(H) x 30(D) Dimensions:

85 gms Weight:

Dimensions: 124(W) x 40(H) x 30(D) 85 gms Weight:

Dimensions: 206(W) x 56(H) x 44(D)

270 gms Weight:

Dimensions: 206(W) x 56(H) x 44(D) 290 gms Weight:

- · Compact installer friendly design.
- For use with GET low voltage luminaires.
- 5 year guarantee.

Transformers - Performer Plus



Code	Description	Qty
GTRE65P	65VA electronic dimmable transformer	1
GTRE105P	105VA electronic dimmable transformer	1
GTRE150P	150VA electronic dimmable transformer	1
GTRE200P	200VA electronic dimmable transformer	1

124(W) x 40(H) x 30(D) Dimensions: Weight: 85 gms


124(W) x 40(H) x 30(D) Dimensions: Weight: 85 gms

Dimensions: 206(W) x 56(H) x 44(D) Weight: 280 gms

206(W) x 56(H) x 44(D) Dimensions:

300 gms Weight:

- · Compact installer friendly design.
- · For use with GET low voltage luminaires.
- · Resettable thermal cut out switch.
- Power on LED indicator.
- · Unique central earthing posting system.
- 10 year guarantee.



Junction box



Code	Description	Qty
GJBN20ASBR	59mm 20A 4 terminal junction box (designed to fit through standard cut-out)	10

Light | Indoor lighting | Downlighters Recessed wall, ceiling and stairs



Ceiling IP54 round luminaire





Code	Description	Qty
GDLCRF1LB	1W LED blue	1



Cut-out: 75mm diameter Mounting depth: 100mm 100mm diameter Dimensions: Requires LED driver (see LED accessories)

GDLCRF1LW 1W LED white Lamp supplied

Cut-out: Mounting depth: 100mm 100mm diameter Dimensions: Requires LED driver (see LED accessories)

GDLCRF40G 40W G9 240V round flat cover Lamp: G9 halogen (not supplied)

Cut-out: 75mm dia Mounting depth: 100mm Dimensions: 100mm diameter

GDLCRF50C 50W capsule 12V G6.35 capsule (not supplied) Lamp:

Cut-out: Mounting depth: 100mm Requires low voltage transformer (GET part no: GTRE65P)

GDLCRF50M 50W (max.) Lamp: MR16 (not supplied)

Cut-out: 75mm dia Mounting depth: 100mm Requires low voltage transformer (GET part no: GTRE65P)



Ceiling square luminaire



GDLCSF40G

GDLCRF40G



GDLCSF50C

GDLCRF50C

Code	Description	Qty
GDLCSF1LB	1W LED blue	1

round flat cover

Lamp supplied

Cut-out: 77 x 77mm Mounting depth: 120mm Dimensions: 89mm x 89mm Requires LED driver (see LED accessories)

GDLCSF1LW 1W LED Lamp supplied

Cut-out-77 x 77mm Mounting depth: 120mm Dimensions: 89mm x 89mm Requires LED driver (see LED accessories)

GDLCSF50M 50W (max.) 12V

Lamp: MR16 (not supplied) Cut-out: 77 x 77mm Mounting depth: 120mm Dimensions: 89mm x 89mm Requires low voltage transformer

(GET part no: GTRE65P)

GDLCSF40G 40W 240V G9 halogen (not supplied) Lamp:

Cut-out: 77 x 77mm Mounting depth: 120mm Dimensions: 89mm x 89mm

GDLCSF50C 50W (max.) 12V Lamp: G6.35 capsule (not supplied)

Cut-out: 77 x 77mm Mounting depth: 120mm Dimensions: 89mm x 89mm Requires low voltage transformer (GET part no: GTRE65P)





- · Die cast construction
- IP54 for bathroom use (round only)
- LED units in blue or white (150,000 hours life)
- Snap-fit cover plates (square units only)
- · LED units feature snap-fit connectors for

quick and easy installation

See page 125 for low voltage transformers. For technical information see page 193



Contemporary recessed luminaires for walls, stairs and ceilings.

Light | Indoor lighting | Downlighters **Cover plates**



Wall Square Luminaire





Code	Description	Qty
GDLWSF1LB	1W LED blue square flat cover	1
GDLWSF1LW	1W LED white square flat cover	1
GDLWSR1LB	1W LED blue square recessed cover	1
GDLWSR1LW	1W LED white square recessed cover	1

Lamp supplied

Plasterboard 78mm x 72mm Cut-out:

Solid wall 79mm x 115mm

Mounting depth: 40mm Dimensions: 89mm x 89mm

Requires LED driver and link cable

(see LED accessories)

 Wall units supplied complete with wall mounting box



Replacement cover plates







Code Description Qty **GDLFCSC** Square with circles cover pattern 1 **GDLFCSL** Square louvre

GDLFCSW Square with window cover pattern1 **GDLFCSP** Square floating glass

Dimensions:

• Interchangeable with all square wall and ceiling fittings





LED accessories





Code	Description	Qty
GDDR	LED driver – powers up to a maximum of eight individual 1W LED luminaires	1
GDLC	1.5m LED link cable	1

1.5m LED link cable Use when operating more than 1 luminaire from GDDR driver. Requires 2 cables for 2 luminaires, 3 cables for 3 luminaires, 4 cables for 4 luminaires, etc.

This cable is not required when operating only one luminaire.

Dimensions (mm): L167 x W39 x D30



Typical installation



Wall versions supplied complete with mounting box.





Light | Indoor Lighting Cabinet and undershelf range

A traditional range of low voltage cabinet lighting and mains voltage striplights. Our cabinet lights are available in 3 finishes and in single or 3 piece kit formats, the kit comes complete with electronic transformer. Striplights (page 130) are available in 2 sizes with and without switch (pull and push).

New for 2007 is a range of mini batten link lights designed for under cabinet and display lighting applications. The fittings can be linked either directly or by the extension cable enabling complete flexibility.

Features and benefits

Mini batten link lighting

All mini battens can be inter connected directly or by using the link cable (supplied)

Supplied with triphosphor fluorescent tube

Available in 5 lengths

Electronic flicker free operation

Cabinet lights

Available in single or 3 piece kit

Supplied complete with G4 lamps

Electronic dimmable transformers with thermal protection supplied with kits

Luminaires supplied with removable mounting collar for surface or flush mounting 3 finishes: white, chrome and brass

Easy to fit plug and socket system

Striplights

Available in 2 sizes (221mm and 284mm)

Slimline design

With or without switch

Switched versions available with push or pull switching

Light | Indoor lighting Mini batten link lighting



Under cupboard link lighting



GT4FL6W35	Mini batten link light - 6W	1
GT4FL10W35	Mini batten link light - 10W	1
GT4FL16W35	Mini batten link light - 16W	1
GT4FL20W35	Mini batten link light - 20W	1


GT4FL30W35 Mini batten link light - 30W 1

500mm link cable


1m link cable

Description

Qty







LINK500

LINK1M

Code



Features:

- · Supplied with linking cable
- All mini battens can be interconnected directly or with link cable (supplied)
- Electronic flicker free operation
- Supplied with 3500K triphosphor white tube
- Full fitting instructions and fixing kit included BS EN 60598



Replacement lamps



Code	Watts	Volts	Qty
T4FL6W35	6W	230V	10
T4FL10W35	10W	230V	10
T4FL16W35	16W	230V	10
T4FL20W35	20W	230V	10
T4FL30W35	30W	230V	10

Length: 11" 275mm Length: 16" 400mm Length: 20" 500mm Length: 25" 625mm
Length: 30" 760mm

Light | Indoor lighting Cabinet and undershelf range



Low voltage cabinet lights (lamp included)



Code	Description	Qty
GDLLC20B	20W Brass	1
GDLLC20C	20W Chrome	1
GDLLC20W	20W White	1

GDLLC20W	20W White	
1		

• Single

Single lights have 1.5m cable (no connectors)

G4 halogen capsule

28mm depth (surface mounted)

70mm diameter

Ceiling depth: 20mm (flush mounted)

187gms

 Removable mounting collar for surface or flush mounting

BS EN 60598-1

Frosted glass lens

Lamps:

Weight:

Features:

Dimensions:

Low voltage cabinet light kits (lamps included)



Code	Description	Qty
GDLLCK320B	20W Brass kit	1
GDLLCK320C	20W Chrome kit	1
GDLLCK320W	20W White kit	1

Kit contains 3 x 20W light fittings complete with G4 halogen capsule lamps and electronic transformer

Features:

- Easy to fit plug and socket system
- Dimmable electronic transformer includes overload and output short circuit protection

221mm & 284mm striplights (lamp required)



Code	Description	Qty
GSTLIT1	60W 221mm Unswitched	6
GSTLIT1PS	60W 221mm Push switch	6
GSTLIT1PU	60W 221mm Pull switch	6
GSTLIT4	60W 284mm Unswitched	6
GSTLIT4PS	60W 284mm Push switch	6
GSTLIT4PU	60W 284mm Pull switch	6

Lamps: Striplights

Striplights utilise linear incandescent lamps and are perfect for providing complementary lighting. They are normally used under cabinets or cupboards in kitchens.

Features:

- Suitable for wall/ceiling mounting undershelves in kitchens etc
- Slimline design

Shaver lights (lamp included)



Code	Description	Qt
GSHVLIT	60W Tungsten single voltage 230V output	1
GSHVLIT2	60W Tungsten dual voltage 115/230V output	1
GSHVLITFL	11W Fluorescent single voltage 230V output	1
GSHVLITFL2	11W Fluorescent dual voltage 115/230V output	1

Lamps: Striplights
Dimensions:
500mm(L) x 60mm(W) x 70mm(H)

Features

- Stylish modern design blends with any décor
- · Opal diffuser for a softer light
- · Fitted with Earth looping terminal
- Supplied with loose back plate for faster fixing
- 60W fittings provide safe disconnection of lamp contact once the diffuser is removed
- Easy connection method
- Suitable for use in bathrooms Zone 3 (see Zone information page 117)
- Manufactured in flame retardant polycarbonate
- IP20



GSHVLITFL2

A stylish range of four shaver light units are designed to complement even the most modern of bathrooms, the soft lines ensure compatibility with any décor whilst limiting dust and dirt collection. Even light dissipation is achieved through the opal diffuser whilst also providing safe disconnection of lamp contacts (when removed for easy replacement of lamps – 60W variants only).

Careful attention has been paid for fast and easy installation including a removable back plate and terminal access for wiring even after the unit has been fixed to the wall. The range is fully certified to all of the relevant safety standards.


Specifications

- Maximum lamp rating 60W
- Supplied pre-fitted with 284mm striplight or 11W CFL fluorescent lamp
- Manufactured in flame retardant polycarbonate
- Compatible with UK, Europe, Australia and USA regulations
- Complies with BS EN 60598-2-1









Light | Indoor Lighting Bathroom range

Our range of bathroom fittings is designed to provide sophisticated light solutions while offering complete safety within this wet environment. Traditionally a difficult area to illuminate sympathetically, the G9 drum range offers stylish design options using etched glass diffusers to distribute light evenly. All luminaires are IP44 rated and comply with electrical and safety standards.

Features and benefits

40W G9 mains voltage halogen lamps (supplied with fittings)

Etched glass diffusers to distribute light evenly Other lamp options include 25W SES candles

IP44 rated (suitable for use in bathrooms)

Round, square and flush fittings

Suitable for wall or ceiling mounting

This section features:

Decorative wall and ceiling luminaires IP44: G9 halogen and candle lamps Shaver lights: 11W compact and 60W tungsten Shower downlights IP54: Low voltage and GU10

Page 134


Page 132

Page 133

Light | Indoor lighting | Bathroom range Decorative Wall and ceiling IP44



Decorative bathroom lights



Code	Description	Qty	Lamp:	G9 60W (included)
GBDRL	Round large	1	Dimensions:	230 dia x 68mm
GBDRS	Round small	1	Lamp:	G9 25W (included)
			Dimensions:	150 dia x 68mm
GBDSS	Square small light	1	Lamp:	G9 40W (included)
			Dimensions:	150 x 150 x 60mm
GBDSL	Square large light	1	Lamp:	G9 60W (included)
			Dimensions:	230 x 230 x 60mm
GBDRF 🗆	Flushlight	1	Lamps:	2 x 40W candle SES (lamp required)
			Dimensions:	340 dia x 40mm



• G9 mains voltage halogen lamps supplied with fitting

■ Double insulated

Decorative bathroom wall lights



Code	Description	Qty
GBDWB 🗆	Wall light	1

This range has been designed specifically for

the bathroom. The range includes square and

circular options plus a series of modern wall

mounted designs.

In particular the GBDGP distributes light horizontally and a pair of these mounted either side of a mirror provides a great effect.

Lamps:

40W candle SES (lamp required)

265 x 155 x 89mm Dimensions:

Features:

- All options are surface mounted
- Luminaires have a variety of finishes and use etched glass diffusers to distribute light
- Other lamp options include 25W and 40W SES candles
- Suitable for use in bathrooms in zone 2 or 3



Light | Indoor lighting | Bathroom range **Shaver lights**



Shaver lights (lamp included)




Code	Description	Qty
GSHVLIT	60W Tungsten single voltage 230V output	1
GSHVLIT2	60W Tungsten dual voltage 115/230V output	1
GSHVLITFL	11W Fluorescent single voltage 230V output	1
GSHVLITFL2	11W Fluorescent dual voltage 115/230V output	1

Lamps: 60W Striplights or 11W CFL fluorescent (lamps included)

Dimensions:

500mm(L) x 60mm(W) x 70mm(H)







A stylish range of four shaver light units are designed to complement even the most modern of bathrooms, the soft lines ensure compatibility with any décor whilst limiting dust and dirt collection. Even light dissipation is achieved through the opal diffuser whilst also providing safe disconnection of lamp contacts (when removed for easy replacement of lamps - 60W variants only).

Careful attention has been paid for fast and easy installation including

a removable back plate and terminal access for wiring even after the unit has been fixed to the wall. The range is fully certified to all of the relevant safety standards.

in Zone 3.

Features

- Stylish modern design blends with any décor
- · Opal diffuser for a softer light
- · Fitted with Earth looping terminal
- Supplied with loose back plate for faster fixing
- · 60W fittings provide safe disconnection of lamp
- contact once the diffuser is removed
- Easy connection method
- · Suitable for use in bathrooms Zone 3 (see Zone information below)
- · Manufactured in flame retardant polycarbonate
- IP20

Specifications


- Maximum lamp rating 60W
- · Supplied pre-fitted with 284mm striplight or 11W CFL fluorescent lamp
- · Manufactured in flame retardant polycarbonate
- · Compatible with UK, Europe, Australia and USA regulations
- · Complies with BS EN 60598-2-1



For lighting installed in Zone 1, all luminaires must be at least IPX4, or IPX5 if water jets are used for cleaning. Mains voltage luminaires can only be used if the circuit is protected by a Residual Current Device having a rated residual operating current not exceeding 30mA. SELV (12V ac) luminaires can be used without RCD protection. The SELV source (transformer) must be located outside Zones 0, 1 and 2, e.g. in the ceiling void.

concealed / protected dual voltage shutter socket





Zome 2

Shaver lights have

Light | Indoor lighting | Downlighters | IP54 Shower lights – low voltage and mains halogen



Low voltage MR16 halogen shower lights (lamp required)



Code	Description (Qty
GDLLS50B	50W 12V MR16 brass	1
GDLLS50C	50W 12V MR16 chrome	1
GDLLS50W	50W 12V MR16 white	1
GDLLS50SS	50W 12V MR16 stainless stee	11
GDLLS50BN	50W 12V MR16 black nickel	1
GDLLS50BS	50W 12V MR16 satin brass	1
GDLLS50PN	50W 12V MR16 pearl nickel	1

Lamp: MR16 (50W max)

Cut-out (mm): 72.5mm
Ceiling Depth: 100mm
Diameter: 83mm

Suitable for use in zone1



Mains voltage GU10 halogen shower lights (lamp included)

Outside present



Code	Description	Qty
GDLGS50B	50W 240V GU10 brass	1
GDLGS50C	50W 240V GU10 chrome	1
GDLGS50W	50W 240V GU10 white	1
GDLGS50SS	50W 240V GU10 stainless st	eel1
GDLGS50BN	50W 240V GU10 black nicke	1 1
GDLGS50BS	50W 240V GU10 satin brass	1
GDLGS50PN	50W 240V GU10 pearl nicke	l 1

Lamp: MR16 (50W max)

Cut-out (mm): 72.5mm
Ceiling Depth: 100mm
Diameter: 83mm




- Suitable for use in bathrooms and shower cubicles
- Clear glass diffuser
- Also suitable for exterior use (IP54 rated), for example on porches
- Die cast construction c/w stirrup and enclosed terminal block
- For use with max 50W MR16 dichroic lamp (not included) or mains voltage GU10 lamp (included)



For lighting installed in Zone 1, all luminaires must be at least IPX4, or IPX5 if water jets are used for cleaning. Mains voltage luminaires can only be used if the circuit is protected by a Residual Current Device having a rated residual operating current not exceeding 30mA. SELV (12v ac) luminaires can be used without RCD protection. The SELV source (transformer) must be located outside Zones 0, 1 and 2, e.g. in the ceiling void.

Bathroom lights must be installed in accordance with IEE regulations, GET's shower range is IP54 rated and can be installed in zones 1, 2 or 3 as specified above (see page 133).

See page 160-161 for lamps.





See also page 126 for IP54 matt steel finish downlights in LED, G9 and low voltage versions.

GDLGS50C

Zone





Light | Indoor lighting | Decorative range

Our new range of spotlights use G9 and GU10 mains voltage halogen lamps in three modern, highly stylish design styles: White circo, Deco and Clear circo. The key benefit of G9 lamp technology means the light head can be smaller to enhance directional control.

The wide choice of decorative fittings – from single spotlight to triple quad ceiling plates – make these ideal for domestic and display lighting applications.

Features and benefits

Fully adjustable heads provide directional light

Wide choice of stylish fittings:

- Single spotlight
- Double bar
- Triple and quad bar and ceiling plates

Three modern styles combining glass and metal Suitable for domestic and

Suitable for domestic and display lighting applications

40W G9 mains voltage halogen lamps supplied with fittings

GU10 lamps supplied with fittings

Styles

White circo: pearl nickel with white circular diffusers

Deco circo: satin nickel clear cubic diffusers

Clear circo: stainless steel with circular diffusers

Light | Indoor lighting | Decorative range GU10 spotlights



Single GU10 spotlights (lamp included)



Code	Description	Qty	L
GCSG1P50C	Single Spot -	1	D
	Polished chrome		W

Lamps: GU10
Dimensions: 80mm diameter

Veight: 0.35kg

Triple plate GU10 spotlights (lamp included)



Code	Description	Qty
GCSG3P50C	Triple Plate – Polished chrome	1
GCSG3P50SGB	Triple Plate – Satin Nickel with blue glass	1

Lamps: GU10
Dimensions: 185mm diameter

1.27kg

Weight:

Triple straight bar GU10 spotlights (lamp included)



Code	Description	Qty
GCSG3B50C	Triple Straight Bar – Polished chrome	1
GCSG3W50SGW	Triple Wave Bar – Satin nickel with white glass	1
GCSG3W50SGB	Triple Wave Bar – Satin nickel with blue glass	1

Lamps: GU10

Dimensions: 100mm centre plate 700mm length

Weight: 1.39kg

Quad wave bar spotlights (lamp included)



Code	Description	Qty
GCSG4W50C	Quad Wave Bar – Polished chrome	1
GCSG4W50SGW	Quad Wave Bar – Satin nickel with white glass	1
GCSG4W50SGB	Quad Wave Bar – Satin nickel with blue glass	1

Lamps: GU10

Dimensions: 100mm centre plate 820mm length

Weight: 1.79kg

Our GU10 spotlights provide a stylish, modern effect in any room. The products are offered in 3 different finishes and are available in four configurations to ensure there is a fitting to satisfy any installation.

The fittings are supplied complete with 50W GU10 lamps (replacement code HD50WGU10) and full instructions and fixing kit.

Features

- Fully adjustable heads
- Choice of single, triple or quad fittings
- Bar and plate designs
- Easy to change lamps
- Supplied complete with 50W GU10 lamps
- Manufactured to BS EN 60598-2-1



Satin nickel with frosted blue glass



Satin nickel with frosted white glass



Polished chrome



Light | Indoor lighting | Decorative range GU10 flat plate spotlights



GU10 flat plate





Code	Description	Qty
GCSGF50B	GU10 flat plate - Brass	1
GCSGF50C	GU10 flat plate - Chrome	1
GCSGF50W	GU10 flat plate - White	1
GCSGF50BN	GU10 flat plate – Black nickel	1
GCSGF50PN	GU10 flat plate - Pearl nickel	1
GCSGF50CB	GU10 flat plate - Brushed chrome	1
GCSGF50BB	GU10 flat plate - Brushed brass	1

Lamps: GU10 50W max (lamps included)

Dimensions: 100mm diameter

Ceiling depth: 75mm

Cut-out: 80mm

A compact and robust range of mains voltage GU10 spotlights for ceiling mounting. The Flat Plate range offers an ideal retrofit for downlighters by utilising existing cut outs. In most cases this allows for a fast upgrade from low voltage to mains voltage GU10 and provides a modern sleek fitting in a variety of finishes.

Features:

- Fully adjustable heads provides directional light (60° max) and no dark ceilings
- · Flat plate recesses up to the ceiling and is secured with spring clips
- · Suitable for retail stores, DIY and display lighting applications
- Drop measurement 125mm



Compact fluorescent downlighters (lamp required)



Floating glass

Code Description Qty Fixed glass cover GDLCS126G Single 26W with fixed glass GDLCS226G Twin 26W with fixed glass

Etched floating glass cover

GDLCS126FG Single 26W with floating glass 1 GDLCS226FG Twin 26W with floating glass 1 Lamps: CFL fluorescent Cut out: 180mm Ceiling depth: 100mm Dimensions:

210mm diameter

Weight: 1.5kg

A highly efficient low energy downlighter using horizontally mounted compact fluorescent lamps. Available in two options, either fixed or a floating glass. The floating glass helps to reflect a little of the light upwards to accent the ceiling and hide the lamp

Features:

- Electro brightened aluminium reflector
- · Pre-wired separate control gear box with easy access for termination
- · Switch start control gear (LPF)
- · Horizontal lamp position
- Use with CFL fluorescent lamp see page 163





Light | Indoor lighting | Decorative range G9 spotlights

Description



G9 spot lights (lamp included)



Code White (pear
GCS9
GCS9
GCS9
GCS










Code		Description	Qty	Lamp	weignt	Dimensions (L x w x H)
	irco style ickel with	white diffusers)				
GCS9R	1PSNFS	1 x G9 Spotlight rectangular base with switch	1	G9	0.5kg	170 x 70 x 100mm (wall mounted)
GCS9R	2PSNF	2 x G9 Spotlight rectangular base	1	G9	0.8kg	150 x 150 x 340mm
GCS9R	3BSNF	3 x G9 Spotlight rectangular base	1	G9	0.9kg	540 x 50 x 170mm
GCS9R	3PSNF	3 x G9 Spotlight round base	1	G9	1.6kg	220 dia. x 170mm
Deco st (satin n	-	clear cubic diffusers)				
GCS9C	1PSNC	1 x G9 Spotlight square base with switch	1	G9	0.5kg	120 x 60 x 100mm (wall mounted)
GCS9C	2BSNC	2 x G9 Spotlight bar	1	G9	0.6kg	360 x 100 x 170mm
GCS9C	3BSNC	3 x G9 Spotlight bar	1	G9	0.7kg	630 x 100 x 143mm
GCS9C	4PSNC	4 x G9 Spotlight square base	1	G9	1.6kg	230 x 230 x 156mm
GCS9C	4BSNC	4 x G9 Spotlight bar	1	G9	2.2kg	890 x 120 x 160mm
	rco style ss steel w	ith clear circo diffusers)				
GCS9G	B2BSNF	2 x G9 Spotlight glass rectangle plate	1	G9	0.7kg	400 x 90 x 170mm
GCS9G	B3PSNF	3 x G9 Spotlight glass triangle plate	1	G9	1.6kg	300 x 300 x 170mm
GCS9G	B3BSNF	3 x G9 Spotlight glass rectangle plate	1	G9	1.6kg	600 x 90 x 170mm
GCS9G	B4PSNF	4 x G9 Spotlight glass square plate	1	G9	1.7kg	260 x 260 x 170mm

G9 mains voltage Halogen lamp in three modern design styles. The G9 lamp used to provide better directional control.



Features:

- · Fully adjustable heads provides directional
- 40W G9 mains voltage halogen lamps supplied with the fitting
- Available in single spotlight, double bar, triple bar and triple and quad ceiling plates the range offers a wide choice of fittings
- · Three styles of fitting are available using a mixture of glass and metal
- · Suitable for both domestic use and display lighting applications



If using a dimmer take the total wattage of the lights and multiply by 2. Treat this as the rated load (wattage) for the dimmer e.g. if using product with 3 x 40W lamps = 120W multiply this by 2 = 240W. The dimmer should therefore be capable of handling a load of 240W.

Single fittings

supplied with

switch

Light | Indoor lighting | Decorative range Ceiling flushlight and uplighter



60W flush lights (lamp required)



Code	Description	Qty
GFLC60B	Brass effect ceiling light	1
GFLC60C	Chrome ceiling light	1
GFLC60W	White ceiling light	1

Lamps: 60W ES

Dimensions: 310mm diameter

(max drop from ceiling 55mm)

Weight: 0.117kg



GFLC60W

Flush lights are ideal ceiling fixtures suitable for bathrooms, offices and corridors and are available in Brass, Chrome and White.

Features:

- · Suitable for wall/ceiling mounting
- Slimline design
- 60W ES fitting suitable for use with GLS/Golfball/Candle lamps
- Decorative opal glass diffuser for even light



40W mains voltage uplighter (lamp required)



Code	Description	Qty
GBDWO	Candle uplighter in stainless steel finish	1

This open uplighter uses a single 40W SES

candle lamp and is ideal for domestic and


1 x 40W SES candle Dimensions: (H x W x D)


65mm x 275mm x 80mm

Weight: 0.4kg

Features:

Wall mount only









Light | Indoor lighting | Fluorescent battens and diffusers

The range of fluorescent battens from GET is the ideal choice for commercial, industrial or domestic installations – combining quality, style, ease of installation and value for money.

- · High impact moulded lamp holder end cap assemblies
- · Powder coated steel casing for durability and enhanced rigidity
- High temperature cable for electrical safety
- High quality starter for reliability and long life
- Large terminal connectors and cable entry for ease of wiring
- Approved ballasts for long operational life and low noise emissions
- Easy fit cover tray, simply turn the twist lock at each end of the batten for fuss free installation and maintenance without the use of a tool
- High quality long life power factor correction capacitor (HPF versions)



Slimline range of battens can be mounted direct to ceiling, walls or suspended by chain or conduit



The innovative design of both the round and square diffuser kits allow for installation on existing GET battens without the need to either remove or rewire the fitting



Additional accessories include square and round prismatic diffusers and reflectors



High frequency batten options for energy efficiency



Light | Indoor lighting Fluorescent battens and diffusers



Bare batten - low power factor (complete with lamp)



Code	Description	Wattage	Qty
LP118LPF	650mm (2ft) single	18W	1
LP218LPF	650mm (2ft) twin	18W	1
LP136LPF	1225mm (4ft) single	36W	1
LP236LPF	1225mm (4ft) twin	36W	1
LP158LPF	1525mm (5ft) single	58W	1
LP258LPF	1525mm (5ft) twin	58W	1
LP170LPF	1790mm (6ft) single	70W	1
LP270LPF	1790mm (6ft) twin	70W	1

- · Supplied with white 35 T8 fluorescent tubes
- · Durable slim line steel construction
- · Width of base 54mm
- Simple 90° turn twist toggles allow for easy access to the gear tray without the need for
- · Large terminal blocks for fast and easy cable connection
- · High quality epoxy powder coated finish
- UV stabilised, non colouring, high impact end cap assemblies
- End cap knockouts no special tool or end cap drilling required
- · Low and high power factor battens for general use
- · Emergency available to order (high power factor only)

Volts: 240V





Bare batten - high power factor (complete with lamp)



Code	Description	Wattage	Qty
LP118HPF	650mm (2ft) single	18W	1
LP218HPF	650mm (2ft) twin	18W	1
LP136HPF	1225mm (4ft) single	36W	1
LP236HPF	1225mm (4ft) twin	36W	1
LP158HPF	1525mm (5ft) single	58W	1
LP258HPF	1525mm (5ft) twin	58W	1
LP170HPF	1790mm (6ft) single	70W	1
LP270HPF	1790mm (6ft) twin	70W	1

Bare batten - high frequency (complete with lamp)



Code	Description	Wattage	Qty
LP136HF	1225mm (4ft) single	36W	1
LP236HF	1225mm (4ft) twin	36W	1
LP158HF	1525mm (5ft) single	58W	1
LP258HF	1525mm (5ft) twin	58W	1
LP170HF	1790mm (6ft) single	70W	1
LP270HF	1790mm (6ft) twin	70W	1

- No visible flicker
- No audible noise
- First time starting
- Reduced running cost (typically 25% energy savings)
- Lower weight
- Easier maintenance
- · Further power factor improvement
- up to 5% increase in lumen performance
- Longer lamp life
- Emergency available to order

Volts: 240V



Square diffusers





Code	Description	Qty
LPSK118	650mm (2ft) single	2
LPSK218	650mm (2ft) twin	2
LPSK136	1225mm (4ft) single	2
LPSK236	1225mm (4ft) twin	2
LPSK158	1525mm (5ft) single	2
LPSK258	1525mm (5ft) twin	2
LPSK170	1790mm (6ft) single	2
LPSK270	1790mm (6ft) twin	2

- · Prismatic acrylic diffuser for low glare soft light
- No special tooling required for installation and maintenance
- For use with GET battens
- Includes lipped cover tray for snug fit which minimises insect ingress and reduces routine cleaning
- · UV stabilised high impact end caps which do not allow light to penetrate

Round diffusers





Code	Description	Qty
LPDK118	650mm (2ft) single	2
LPDK218	650mm (2ft) twin	2
LPDK136	1225mm (4ft) single	2
LPDK236	1225mm (4ft) twin	2
LPDK158	1525mm (5ft) single	2
LPDK258	1525mm (5ft) twin	2

- · Prismatic acrylic diffuser for low glare
- · No special tooling required for installation and maintenance
- For use with GET battens
- · Provides lower light loss than conventional square diffusers
- · UV stabilised high impact end caps which do not allow light to penetrate


Metal reflectors



Code	Description	Qty
LPRK36W	1225mm (4ft) single	4
LPRK58W	1525mm (5ft) single	4
LPRK70W	1790mm (6ft) single	4

- · Suitable for single and double tube battens
- · Powder coated steel for a smooth durable finish
- · Broad lighting distribution
- · For use with GET battens





Our outstanding range of amenity luminaires has been designed to encompass durability with good design together with excellent lighting performance.

Our products have been designed with the contractor in mind and are quick and easy to install.

A unique feature of the GET range – our drum range have a surface wiring facility as well as a hinged demountable gear tray.

The range is complemented with the introduction of high frequency models.

Light | Outdoor lighting | Amenity range

Features and benefits **Specification** Range of ten CFL energy saving Low level 20mm conduit entries IP65 rated High quality weather resistant compact fluorescent fittings for easy installation neoprene sealing gasket Black and white base with complete with lamps Unique surface wiring facility four screws for improved **Opal or Prismatic diffusers** Wall and ceiling mounting sealing and security Compact fluorescent lamp Voltage 240V options included with fitting for low BESA box mounting **Emergency options** High IP65 rating for indoor installation and running costs available to special order and outdoor use Suitable for pedestrian F marked Tough UV stabilised corridors, stairwells, polycarbonate body for subways and general Class 1 vandal resistance amenity / security areas Hinged, demountable gear Emergency drums have an **Amenity ranges** tray for easy wiring integral 3 hour battery back up **Drum luminaires** Page 143 Bukheads and bricklights, Page 144 Page 144 Floodlights and PIRs

Light | Outdoor lighting | Amenity range Drum range – IP65



Compact fluorescent drums - switch start (2 pin lamp included)







Code
White base GDFRS16WWO GDFRS16WWP GDFR16WWO GDFR16WWP GDFR28WWO GDFR28WWP
GDFS16WWP GDFS16WWP GDFS28WWO GDFS28WWP
Black base GDFRS16WBO


Black base GDFRS16WBO
GDFRS16WBP
GDFR16WBO
GDFR16WBP
GDFR28WBO
GDFR28WBP
GDFS16WBO
GDFS16WBP
GDFS28WBO
GDFS28WBP

Description	Qty
16W round drum	1
16W round drum	1
16W large round drum	1
16W large round drum	1
28W large round drum	1
28W large round drum	1
16W large square drum	1
16W large square drum	1
28W large square drum	1
28W large square drum	1



Lamp: 2 pin compact double D

Opal diffuser	255mm diameter
Prismatic diffuser	255mm diameter
Opal diffuser	285mm diameter
Prismatic diffuser	285mm diameter
Opal diffuser	285mm diameter
Prismatic diffuser	285mm diameter
Opal diffuser	255 x 255mm
Prismatic diffuser	255 x 255mm
Opal diffuser	255 x 255mm
Prismatic diffuser	255 x 255mm
Opal diffuser	255mm diameter
•	
Prismatic diffuser	255mm diameter
Opal diffuser	285mm diameter
Priematic diffuser	285mm diameter





Emergency compact fluorescent drums with integral battery back-up - high frequency (4 pin lamp included)








Code	Description	Qty
White base		
GDFR16WWOE	16W large round drum	1
GDFR16WWPE	16W large round drum	1
GDFR28WWOE	28W large round drum	1
GDFR28WWPE	28W large round drum	1
GDFS28WWOE	28W large square drum	1
GDFS28WWPE	28W large square drum	1
Black base	10\\\\	4
GDFR16WBOE	16W large round drum	- 1

GDFR16WBOE	16W large round drum
GDFR16WBPE	16W large round drum
GDFR28WBOE	28W large round drum
GDFR28WBPE	28W large round drum
GDFS28WBOE	28W large square drum
GDFS28WBPE	28W large square drum

Lamp: 4 pin compact double D

Opal diffuser	285mm diameter
Prismatic diffuser	285mm diameter
Opal diffuser	285mm diameter
Prismatic diffuser	285mm diameter
Opal diffuser	255 x 255mm
Prismatic diffuser	255 x 255mm

Opal diffuser	285mm diamete
Prismatic diffuser	285mm diamete
Opal diffuser	285mm diamete
Prismatic diffuser	285mm diamete
Opal diffuser	255 x 255mm
Prismatic diffuser	255 x 255mm



- constructionHinged gear-tray for quick easy installation
- Unique easy-seal surface wiring facility

Vandal resistant all-polycarbonate

- Low-level positioned 20mm conduit entries no conduit bending needed
- IP65 for outdoor and indoor use (including bathroom Zone 1)
- Four screw positive cover fixing to maintain IP65 integrity
- Supplied complete with 16 and 28W lamps (colour 3500K)
- BESA box fitting facility
- F marked

Features:

Emergency Luminaires:

- · 3 hour self contained maintained
- 4 pin 16 and 28W 3500K lamp included

Light | Outdoor lighting | Amenity range Bulkheads, bricklights & floodlighting



Bulkheads (lamp required)





Code	Description	Qty
GBH100BC	100W with clear diffuser	1
GBH100BR	100W with red diffuser	1
GBH29C	2 x 9W CFL with clear diffuse	r 1
GBH29CP	2 x 9W CFL with photocell and clear diffuser	1
GBH60BC	60W economy with clear diffuser	1

Bulkheads are a tough reliable solution to provide light for safety and security. They come with a choice of GLS and Energy Saving lamp options and also have a unit with a photocell that illuminates at a preset light level.

GBH60BCPC 60W bulkhead with cover

Lamps: BC GLS or 9W CFL energy saving

Features:

- · Choice of GLS or energy saving options
- · Manufactured from die-cast aluminium
- · Powder coated paint finish for extra durability
- · Corrosion resistant
- Tough UV stabilised polycarbonate cover
- Choice of 20mm knockouts for cable and/or conduit entry
- Suitable for use in exterior application such as walkways and paths
- Can also use energy saving lamps (see page 163)



Photocell





Code	Description	Qt
GPC500C GPC500CK	Clear electronic photocell Clear electronic photocell kir	t

Photocell kit comprises photocell head, mounting bracket and fixings.

· Electromagnetic relay

• Load: 2 x 250W HPS typical

• Max capacity: 5A/60µf

• On/off levels: 70/105 Lux (1:1.5 + VE)

• IP rating: IP65

BS 5972



40W Bricklights (lamp required)



Code	Description	Qty
GBL40LB	40W louvered black	1
GBL40PB	40W plain black	1

Bricklights are a great solution to recess fittings flush to the wall for added security. The louvered option is very tough and provides a degree of vandal resistance and can be used to provide good low level lighting when mounted near paths, driveways and car park

Lamps: Decorative round, candle or energy

Features:

- IP44 rated
- · Manufactured from die-cast aluminium
- · Powder coated paint finish for extra durability
- · Corrosion resistant
- Suitable for lighting paths & driveways
- · Suitable for use in exterior application
- · Can also use energy saving lamps (see page 163)



Floodlighting and PIRs (lamp required unless stated)





	L	4	
EXPIR			
Caa maga 140	for lamana		


Code	Description	Qty
P/MINIV	150W vertical mini PIR TH floodlight c/w 150W lamp	1
GXPIRFD	500W professional 180° PIR floodlight c/w 500W lamp	1
EXPIR	500W independent PIR unit	1
MINI/FLDV	150W compact enclosed TH floodlight	1
GPIRTWB	Twin 120W PAR 38 floodlight with PIR	1

Lamps: Linear tungsten, halogen & PAR 38

- BS 4533 & BS EN 60730
- Can also use energy saving lamps (see page 163)

See page 148 for lamps.





Our range of low voltage stone effect bollards and postlights with their distinct clear white light are ideal for sign-posting walkways and drives. They not only look good but are also extremely cost effective to run.

Low voltage options extend to stainless steel postlights and pagodas to add that sophisticated touch within our ever expanding range. We guarantee that whether you want a more traditional or modern fitting there are styles and finishes to suit everyone.

Light | Outdoor lighting | Low voltage

Styles available

Stone effect bollards and postlights

Die-cast cap lights and stormglass postlights

Halo postlights and Japanese lantern pagodas

Die-cast bollards

Stainless steel pagodas and postlights:

Fitted with 0.5m of SPT-1 cable

Both single units and kits are available

Suitable for decking, drives, pathways and walls

Each fitting complete with **EZClick** connector

3 year guarantee



Light | Outdoor lighting EZClick low voltage lighting system



EZClick accessories

Step by step guide

The EZClick low voltage lighting system from GET is as simple as it sounds. No confusing wiring to be done at all. Simply connect the fittings to the low voltage cable with special connector blocks and plug in the transformer.

Step 1: Plan your design



Step 2: Select your light fittings







Step 3: Select the appropriate cable length




Step 4: Select an appropriate transformer by adding together the wattage of your chosen fittings



Step 5: Position fittings along the length of cable and include timer or PIR if desired





Code	Description
Couc	Dooonpac

GGLLPT	PIR with timer (require
	GGLLJ32 connectors)
GGLLT	Timer (require GGLLJ32
	connectors)

Transformers	
GGLLTR60	60VA Transformer with
	screw connector
GGLLTR105	105VA Transformer with
	screw connector

15 metre SPT-1 cable
15 metres x SPT-3 cable
with screw connector
25 metres x SPT-3 cable
with screw connector

Lamps & accessories

GGLLL10W	2 x 10W spare wedge
	lamps

GGLLL10MR11 2 x 10W MR11 lamps

EZClick connectors

GGLLJ31	2 x garden light 3-1
	connectors
GGLLJ32	2 x garden light 3-2
	connectors (for use wit
	GGLLPT & GGLLT)
GGLLJ11	2 x garden light 1-1
	connectors

• Timer has 3 settings, dusk to dawn, 3 hour or PIR to provide a wide choice of possible selections

Dimensions:

102 (L) x 63 (W) x 75mm (D) 60VA

120 (L) x 80 (W) x 75mm (D) 105VA

15m cable to extend GGLLMC315M (or GGLC325M), requires 1 x GGLLJ31 connector

- Connectors use a numbering system that applies to the diameter of the SPT cable. ie a GGLLJ31 is a 3-1 connector will connect one piece of SPT3 cable to SPT1 cable
- · Fully weatherproof
- IP44

Light | Outdoor lighting | LED Decklights, pebbles & sticks



LED decklight kit - 4 twin LED light units



Code	Description	Q
GGLLLEDK4W	LED decklight kit with stainless steel finish and 4 twin LED light units, 10m cable, low voltage transformer, connectors and a 25mm drill bit	

Lamp Colour: White

Features

- LED Life of up to 100,000 hours (non replaceable)
- Operate cool safe to touch when operating (safe for children/pets)
- Fully compatible with GET low voltage cable and transformers to add into an existing system
- Includes 12V 10VA transformer
- Up to 20 LEDs can be run on the transformer supplied
- Illuminate step edges for added safety
- Decorate your decking/flooring
- LED's are less damaging to the environment than incandescent lamps as they use up to 90% less energy

 | ENERGY | SAPE | SAP

Add-on units - for use with GET LED decklight kit



EZClick connector



Code	Description	Qty
GGLLLED1W	LED decklight add-on	1
GGLLLED1G	LED decklight add-on	1
GGLLLED1A	LED decklight add-on	1
GGLLLED1B	LED decklight add-on	1
GGLLLED1R	LED decklight add-on	1

Lamp colour : Green Lamp colour : Amber Lamp colour : Blue Lamp colour : Red

Lamp colour: White

Features

 Each LED uses 0.3W of power so up to 20 can be used instead of one 10W lamp in a typical low voltage installation

As used on the LED decklights

White LED Pebble Kit



Code	Description	Qty
GGLLLEDK10P	10 white pebble kit	1

- 12V low voltage fitting
- 10 White LED pebbles (permanently fixed to cable)
- 15m cable, pebbles spaced 0.5m apart over the last 5m
- Indoor plug in transformer included
- Suitable for indoor or outdoor use



LED Acrylic Sticks



Code	Description	Qty
GGLLLEDKT	single LED acrylic stick	1
GGLLLEDK4T	LED Acrylic 4 stick kit	1

each light contains 2 bright white LED's fitted with 0.5m of SPT-1 cable approx and EZClick connector

Overall height 320mm (200mm of acrylic & 120mm of metal tube)

kit includes:

- 4 acrylic sticks, 15m SPT-1 Cable and an indoor transformer each light fitted with 0.5m of SPT-1 cable approx and EZClick connector
- Up to an additional 20 acrylic stick lights can be added to this system



Light | Outdoor lighting | Low voltage Pagoda, spotlight kits, postlights & festoons

Pagoda kit



Pagoda & spotlight kits



Code	Description	Qty
GGLLK4P	4 pagoda kit	1
GGLLK4S	4 spot kit	1

Pagoda and spotlight kit features:

- · Kit of four fittings supplied c/w transformer and 15m SPT-2 cable
- 3 year guarantee





Stainless steel post lights





Code	Description	Qty
GGLLLPS	Stainless steel pagoda	1
GGLLPRS10	Stainless steel postlight	1
	with shade rings	
GGLLPS10	Stainless steel postlight plain	1



- Lamps: 10W wedge
- Suitable for decking, pathways and walls
- Lamp type: 10W Wedge lamp (postlight) and 10W JC (pagoda)
- Fitted with 0.5m of SPT 1 cable approx and EZClick connector
- 3 year guarantee
- · Diecast spike for use in borders, lawns and gravel drives etc.





Tall postlights



Code	Description	Qty
GGLMLP20	3 head tall postlight modern style in antique bronze finish	1

Lamps: G4 20W

Dimensions: 2005 (H) x 605mm (W)

- Includes 20W G4 lamps and a 60VA transformer located in the base of the fitting
- Easy installation (12V) requires no steel armoured cable
- Can be connected into system using **EZClick** connectors



For weights and dimensions please see technical section page 192

Light | Outdoor lighting | Low voltage Deck lights, spotlights & bollard lights



Deck lights, spotlights & bollards



Code	Description	Qty				
GGLLDDV	Deck downlighter	1	Colour:	Verdigris	Lamp:	10W wedge
GGLLDDB	Deck downlighter	1	Colour:	Black	Lamp:	10W wedge
GGLLDUV	Deck uplight	1	Colour:	Verdigris	Lamp:	20W MR16
GGLLDUB	Deck uplight	1	Colour:	Black	Lamp:	20W MR16
GGLLDUS	Deck uplight	1	Colour:	Stainless steel	Lamp:	20W MR16
GGLLSPPB	Diecast spotlight	1	Colour:	Black	Lamp:	20W MR16
GGLLSPPV	Diecast spotlight	1	Colour:	Verdigris	Lamp:	20W MR16
GGLLBPT	Diecast bollard light	1	Colour:	Titanium	Lamp:	10W JC TH
GGLLBPB	Diecast bollard light	1	Colour:	Black	Lamp:	10W JC TH
GGLLBPV	Diecast bollard light	1	Colour:	Verdigris	Lamp:	10W JC TH



Die-cast spotlight

GGLLBPV





Deck uplight



Dimensions:


Downlighter: 136mm diameter Decklighter: 105mm diameter 20mm height

120 (H) x 150mm (W) Spotlight: 250 (H) x 166mm (W) Bollard:

Features:

- Wall mounting
- Lamp type: 10W Wedge lamp
 Fitted with 0.5m of SPT 1 cable approx and EZClick connector
- For weights and dimensions please see technical section page 192
- 3 year guarantee

Die-Cast Spotlight



See also our LED Decklight kit on page 147. Up to 20 LED fittings can be run on the transformer supplied with the kit. Alternatively up to 20 LED fittings can be substituted for one 10W low voltage light on the circuit. They both use the EZClick connector and cable system.





Light | Outdoor lighting | Low voltage Stone effect postlight & 6 sided lanterns



Stone effect postlight & bollards (includes lamp)



Code	Description	Qty	
GGLLSRP	Round postlight	1	Lamps: 20W MR16
GGLLSRB	Round bollard light	1	Lamps: 10W wedge lamp
GGLLSSTB	Square bollard with glass tier diffuser	1	Lamps: 20W MR16

Features:

- 12V Low voltage fitting
- · Clear white halogen light
- Suitable for mounting on decking, pathways and walls
- Fitted with 0.5m of SPT 1 cable approx and **EZClick** connector
- For weights and dimensions please see technical section page 192
- 3 year guarantee

Square bollard



Kit options (triple packs - includes lamps)

Code	Description	Qty	Lamps: 10W wedge
GGLL6PBK3	6 sided lantern postlight kit supplied c/w cable and transformer	3	Colour: Black
GGLL6HB3 GGLL6HV3	Crooklight kit Crooklight kit	3 3	Colour: Black Colour: Verdigris
			All kits contain 3 li and a transformer

- lights, 15m SPT-3 cable
- Fitted with 0.5m of SPT 1 cable approx and *EZClick* connector

6 sided lantern crooklights and wall light (includes lamp)



GGLLSSB





Code	Description	Qty
GGLL6PV	6 sided lantern postlight	1
GGLL6PB	6 sided lantern postlight	1
GGLL6PT	6 sided lantern postlight	1
GGLL6HV	6 sided lantern crooklight	1
GGLL6HB	6 sided lantern crooklight	1
GGLL6HT	6 sided lantern crooklight	1
GGLL6WV	6 sided lantern wall light	1
GGLL6WB	6 sided lantern wall light	1
GGLL6WT	6 sided lantern wall light	1

Colour: Verdigris
Colour: Black
Colour: Titanium
Colour: Verdigris
Colour: Black
Colour: Titanium
Colour: Verdigris
Colour: Black
Colour: Titanium

Features:

- 12V low voltage fitting
- Manufactured from die cast alloy
- Lamp type: 10W Wedge lamp included
- Fitted with 0.5m of SPT 1 cable approx and *EZClick* connector
- For weights and dimensions please see technical section page 192
- 3 year guarantee

Light | Outdoor lighting | Low voltage Stone effect novelty



Stone effect low level spotlights (includes lamp)



GGLLSSH Frog



Code	Description	Qty
GGLLSRO	Rock	1
GGLLSSH	Shell	1
GGLLSSN	Snail	1
GGLLSTU	Turtle	1
GGLLSFR	Frog	1

Features:

- Low Voltage fitting (12V)
- IP68 submersible to 0.5m max.
- 10W MR11 dichroic lamp provides clear white light
- Fitted with 0.5m of SPT-1 cable approx and *EZClick* connector
- 3 year guarantee





Kit options (triple pack, includes lamp)

GGLLSSN

Snail



Baby rock	
MILES 200	
	A STATE OF THE PARTY OF THE PAR
BEATS OF THE REAL PROPERTY.	THE SECOND
	-
GGLLSROK2	THE REST OF THE PARTY OF THE PA

Code	Description	Qty
GGLLSROK3	3 x Rock kit supplied c/w 10m cable & transforme IP68 rated	1 r
GGLLSROK2	2 x Baby rock kit supplied c/w 10m cable & transforme for indoor use	1 r



- Complete with 5W Halogen lamps
- Stone effect resin finish
- Not for outdoor use (best used in conservatories)
- For weights and dimensions please see technical section page 192
- 3 year guarantee





Rock kit for use directly in water features

Light | Outdoor lighting | Low voltage Caplight and stormglass



Diecast caplights & stormglass postlights (includes lamp)



Code	Description	Qty	Lamps: 10W wedge
GGLLCPV	Caplight postlight	1	Colour: Verdigris
GGLLCPB	Caplight postlight	1	Colour: Black
GGLLCPT	Caplight postlight	1	Colour: Titanium
GGLLCHV	Caplight crooklight	1	Colour: Verdigris
GGLLCHB	Caplight crooklight	1	Colour: Black
GGLLCHT	Caplight crooklight	1	Colour: Titanium
GGLLCWV	Caplight wall light	1	Colour: Verdigris
GGLLCWB	Caplight wall light	1	Colour: Black
GGLLCWT	Caplight wall light	1	Colour: Titanium
GGLLSPSB	Diecast stormglass postlight	1	Colour: Black
GGLLSPSV	Diecast stormglass postlight	1	Colour: Verdigris
GGLLSPST	Diecast stormglass postlight	1	Colour: Titanium

Features:

- Low Voltage fitting
- · Manufactured from die cast alloy
- Lamp type: 10W Wedge lamp
- Fitted with 0.5m of SPT 1 cable approx and *EZClick* connector
- · For weights and dimensions please see technical section page 192
- 3 year guarantee
- IP44











Kit options (triple packs - includes lamps)

Code	Description	Qty	
GGLLCPB3	Caplight postlight kit	1	Colour: Black
GGLLCHB3	Caplight crooklight kit	1	Colour: Black

- All kits contain 3 lights, 15m SPT-3 cable and a transformer
- Fitted with 0.5m of SPT 1 cable approx and *EZClick* connector



Products are die-cast from high grade aluminium. By chemical treatment to the chrome, a better surface is obtained for the powder coating that prevents corrosion. By using UV stabilizers in the powder coating the colour will keep its original look for many years.

Light | Outdoor lighting | Low voltage Lanterns and postlights



Diecast decorative lights (includes lamp)



Code	Description	Qty
GGLLHPV GGLLHPB	Halo postlight Halo postlight	1
GGLLHPT	Halo postlight	1
GGLLCHPV GGLLCHPB	Japanese lantern postlight Japanese lantern postlight	1 1
GGLLPHV GGLLPHB	Pagoda crooklight Pagoda crooklight	1 1

Colour: Verdigris
Colour: Black
Colour: Titanium
Colour: Verdigris
Colour: Black
Colour: Verdigris

Dimensions

Halo: 230 (H) x 155mm (W)

Japenese

lantern: 367 (H) x 150mm (W)

Pagoda

crooklight: 452 (H) x 120mm (W)

Features:

- · Low Voltage Fitting
- · Manufactured from die cast alloy
- Lamp type: Postlight 10W JC crooklight
- Lamp type: Crooklight 10W
- Fitted with 0.5m of SPT 1 cable approx and *EZClick* connector
- For weights and dimensions please see technical section page 192
- 3 year guarantee
- IP44







Halo kit



Kit options (triple packs - includes lamps)

Code	Description	Qty
GGLLHPBK3	Halo postlight kit supplied c/w cable and transformer	1
GGLLHPV3	Halo light kit	1

Colour: Black

Colour: Verdigris

- All kits contain 3 lights, 15m SPT-3 cable and transformer
- Fitted with 0.5m of SPT 1 cable approx and *EZClick* connector
- See above for lamp and dimension details
- IP44

Light | Outdoor lighting | Low voltage Pagoda postlights



Die-cast decorative lights (includes lamp)





Code	Description	Qty
GGLLKPS	pagoda post circular top	1
GGLLKPG	pagoda post circular top	1
GGLLKP3RS	pagoda post 3 glass rings	1
GGLLKP3RG	pagoda post 3 glass rings	1
GGLLKP5RS	pagoda post 5 diecast ring	gs 1
GGLLKP5RGY	pagoda post 5 diecast ring	gs 1
GGLLKPPS	pagoda post pyramid top	1
GGLLKPPGY	pagoda post pyramid top	1

colour: silver colour: granite

colour: silver colour: granite

colour: silver

colour: silver

colour: grey

- low voltage fittings
- · manufactured from die cast alloy
- each light fitted with 0.5m of SPT-1 cable approx and *EZClick* connector
- lamp type:- 10W halogen capsule
- IP44

kit options (4 light kit)







Code	Description	Qty
GGLLLK4PS	pagoda post circular top	1
GGLLK4PG	pagoda post circular top	1
GGLLK4P3RS	pagoda post 3 glass rings	1
GGLLK4P3RG	pagoda post 3 glass rings	1
GGLLK4P5RS	pagoda post 5 diecast ring	s 1
GGLLK4P5RGY	pagoda post 5 diecast ring	s 1
GGLLK4PPS	pagoda post pyramid top	1
GGLLK4PPGY	pagoda post pyramid top	1

colour: silver colour: granite

colour: silver colour: granite

colour: silver colour: grey

colour: silver colour: grey

Each kit contains;

- 4 lights each fitted with 0.5m of SPT-1 cable
- 15M cable and 4 connectors
- 4 deck mounting bases and ground spikes
- 10W halogen capsule lamps
- 60VA outdoor transformer
- for weights and dimensions please see technical section page 192

2 extra lights and extra cable can be added





Light | Outdoor lighting | Mains voltage

Mains voltage exterior lanterns can offer simple, traditional styling or more dramatic, contemporary designs. Compatible with a variety of lamp types – from golf ball or candle lamps to energy saving compact fluorescent lamps – post, wall mounting or hanging options also provide the flexibility to mount these highly practical lanterns to suit your specific needs.

Features and benefits

Modern stainless steel postlights

Traditional 6 sided lanterns with glass tops to diffuse light evenly

Modern style wall, post & hanging versions

Steel & copper finishes

Tall postlights in a modern or traditional style with matching wall lights

Light | Outdoor lighting | Mains voltage Tall postlights, wall lights & stainless steel posts



Tall postlights & wall lights (lamp required)



Code	Description	Qty
GGLMLPMBR	3 head tall post light modern antique bronze	1
GGLMCAB	Modern wall light antique bronze	1
GGLMCB	Modern wall light black	1
GGLMCLCAB	Traditional wall light antique bronze	1
GGLMCLB	Traditional wall light black	1

Lamps: BC GLS or BC energy saving

- Can also use energy saving lamps (see page 163)
- 3 year guarantee
- Can also use energy saving lamps
- (see page 163) • 3 year guarantee



Stainless steel posts (lamp required)



Code	Description	Qty
GGLMWRS	Stainless steel wall post	1
GGLMSPRS	Stainless steel short post	1
GGLMTPRS	Stainless steel tall post	1

Lamps: ES or energy saving Dimensions: 340 (H) x 140mm (Dia) Dimensions: 309 (H) x 140mm (Dia) Dimensions: 810 (H) x 140mm (Dia)

Features:

- Lamp type: 60W Max (ES) Golfball or 11W energy saving lamp (see page 148)
- Stainless steel and glass construction · Posts are suitable for decking, pathways
- For weights and dimensions please see
- technical section page 192



Steel & Copper exterior lanterns (lamp required)



GGLMH999G GGLMH999C	Hanging lantern Hanging lantern	1
GGLMWS999G GGLMWS999C	Straight wall lantern Straight wall lantern	1

Description



Code

Lamps: ES, GLS, golfball or candle Colour: Galvanised steel Copper

Dimensions: 875 (H) inc. chain x 270mm (W)

Colour: Galvanised steel Copper

Dimensions: 400 (H) x 270mm (W)

Qty

- · Lamp type: 75W max (ES) GLS, Golfball or Candle lamp
- Galvanised steel / copper & glass construction
- Can also use energy saving lamps (see page 163)
- For weights and dimensions please see technical section page 192

Light | Outdoor lighting | Mains voltage Traditional & modern style lanterns



GLS, golfball, candle or energy saving

Traditional style die cast exterior lanterns (lamp required)





GGLMWU640B



Code	Description	Qty	Lamps: ES, GL
GGLMH640W	Hanging lantern	1	Colour: White
GGLMWU640W GGLMWU640B	Wall up lantern Wall up lantern	1 1	Colour: White Colour: Black
GGLMWD640W GGLMWD640B	Wall down lantern Wall down lantern	1 1	Colour: White Colour: Black
GGLMP640W GGLMP640B	Post top lantern Post top lantern	1 1	Colour: White Colour: Black
GLAN4SB GLAN4SPTB	4 sided lantern 4 sided post top lantern	1 1	Colour: Black Colour: Black
GLAN6SB	6 sided lantern	1	Colour: Black
GLAN6SPTB	6 sided post top lantern	1	Colour: Black

Wall down lantern



Post top lanterns



Traditional style lantern

- Bevelled edge glass for decorative effect
- Ideal for lighting doorways and patios
- Vandal proof construction
- · Die cast construction for durability
- For use with Golfball or Candle lamps
- Weatherproof IP43
- Can also use energy saving lamps (page 163)
- · Lamp type: 60W Max (ES) GLS, Golfball or Candle lamps
- 4-6 sided lantern features:
- Lamp type: 60W Max (ES) GLS, Golfball or Candle lamps
- Die cast and glass construction
- Can also use energy saving lamps (page 163)

Modern style die cast exterior lanterns (lamp required)



Code	Description	Qty
GGLMH540W	Hanging lantern	1
GGLMH540B	Hanging lantern	1
GGLMH540T	Hanging lantern	1
GGLMWU540W	Wall up lantern	1
GGLMWU540B	Wall up lantern	1
GGLMWU540T	Wall up lantern	1
GGLMWD540W	Wall down lantern	1
GGLMWD540B	Wall down lantern	1
GGLMWD540T	Wall down lantern	1
GGLMP540W	Post top lantern	1
GGLMP540B	Post top lantern	1
GGLMP540T	Post top lantern	1



Wall up lantern

GGLMWU540B

Lamps: ES, GLS, golfball or candle

White Colour: Black

Titanium

Dimensions: 240 (W) x 255mm (D)

White Colour:

Black

Titanium

Dimensions: 340 (H) x 240mm (W)

White Colour: Black

Titanium

Dimensions: 400 (H) x 240mm (W)

White Colour:

Black

Titanium

Dimensions: 395 (H) x 240mm (W)

Features:

- Lamp type: 60W max (ES) GLS, Golfball or Candle lamps
- · Die cast and polycarbonate construction
- Can also use energy saving lamps (see page 164)
- For weights and dimensions please see technical section page 192





Light | Lamps range

Range overview



Incandescent (Pages 159-160)

- Universal lamp satisfying diverse lighting requirements.
- Easily dimmable
- Flexible and versatile with no need for electronic starting and control systems
- · Pearl, clear and soft white
- Bayonet and screw caps



Halogen (Pages 161-162)

- Compact crisp white uniform light output
- Dimmable
- Uses energy more efficiently
- Longer life
- Small filaments give better beam control for directional light
- Mains and low voltage



Compact fluorescent (Page 163)

- Low energy consumption and maintenance
- Perfect choice for use in slim luminaires
- Suitable for up-lighting and down-lighting
- Colour temperatures warm white 2700K and white 3500K



Striplights (Page 162)

- Double ended tubular lamp
- Suitable for use with shaver light units
- · Opal or clear



Energy saving (Page 163)

- Low energy consumption and maintenance
- Retrofit designs to replace incandescent lamps
- Wide range of wattages and sizes
- · Incandescent equivalent wattage listed



T4 & T5 Miniature fluorescent (Page 164)

- High energy efficiency
- Colour temperatures cool white 3300K and white 3000K
- Wide range of wattages and lengths

Light | Lamps range Incandescent




GLS

Code	Watts	Volts		
GLSNL12WCLBC	nightlight 12W	240V	Cap: BC	Finish: Clear
GLS40WCLBC	40W	240V	Cap: BC	Finish: Clear
GLS40WPBC	40W	240V	Cap: BC	Finish: Pearl
GLS40WCLES	40W	240V	Cap: ES	Finish: Clear
GLS40WPES	40W	240V	Cap: ES	Finish: Pearl
GLS60WCLBC	60W	240V	Cap: BC	Finish: Clear
GLS60WPBC	60W	240V	Cap: BC	Finish: Pearl
GLS60WCLES	60W	240V	Cap: ES	Finish: Clear
GLS60WPES	60W	240V	Cap: ES	Finish: Pearl
GLS100WCLBC	100W	240V	Cap: BC	Finish: Clear
GLS100WPBC	100W	240V	Cap: BC	Finish: Pearl
GLS100WCLES	100W	240V	Cap: ES	Finish: Clear
GLS100WPES	100W	240V	Cap: ES	Finish: Pearl

 Universal lamps satisfying diverse lighting requirements

Candle


GLS40WCLBC



Code	Watts	Volts		
CNDL25WCLBC	25W	240V	Cap: BC	Finish: Clear
CNDL25WCLES	25W	240V	Cap: ES	Finish: Clear
CNDL25WCLSBC	25W	240V	Cap: SBC	Finish: Clear
CNDL25WCLSES	25W	240V	Cap: SES	Finish: Clear
CNDL40WCLBC	40W	240V	Cap: BC	Finish: Clear
CNDL40WCLES	40W	240V	Cap: ES	Finish: Clear
CNDL40WSWBC	40W	240V	Cap: BC	Finish: Soft white
CNDL40WCLSBC	40W	240V	Cap: SBC	Finish: Clear
CNDL40WSWSBC	40W	240V	Cap: SBC	Finish: Soft white
CNDL40WCLSES	40W	240V	Cap: SES	Finish: Clear
CNDL40WSWSES	40W	240V	Cap: SES	Finish: Soft white
CNDL60WCLSBC	60W	240V	Cap: SBC	Finish: Clear
CNDL60WCLSES	60W	240V	Cap: SES	Finish: Clear
CNDL60WCLBC	60W	240V	Cap: BC	Finish: Clear
CNDL60WCLES	60W	240V	Cap: ES	Finish: Clear
CNDL60WSWBC	60W	240V	Cap: BC	Finish: Soft white

 Enhance any room using decorative wall or ceiling luminaires with candle lamps

Decorative round (45mm)



Code	Watts	Volts		
G4525WSWSES	25W	240V	Cap: SES	Finish: Soft white
G4525WSWBC	25W	240V	Cap: BC	Finish: Soft white
G4540WCLBC	40W	240V	Cap: BC	Finish: Clear
G4540WSWBC	40W	240V	Cap: BC	Finish: Soft white
G4540WSWES	40W	240V	Cap: ES	Finish: Soft white
G4540WSWSBC	40W	240V	Cap: SBC	Finish: Soft white
G4540WCLSES	40W	240V	Cap: SES	Finish: Clear
G4540WSWSES	40W	240V	Cap: SES	Finish: Soft white
G4560WCLBC	60W	240V	Cap: BC	Finish: Clear
G4560WSWBC	60W	240V	Cap: BC	Finish: Soft white
G4560WSWES	60W	240V	Cap: ES	Finish: Soft white
G4560WSWSBC	60W	240V	Cap: SBC	Finish: Soft white
G4560WCLSES	60W	240V	Cap: SES	Finish: Clear
G4560WSWSES	60W	240V	Cap: SES	Finish: Soft white

• Compact and attractive lamp designed for small decorative luminaires

Light | Lamps range Incandescent and Halogen



Pygmy



Code	Description	Watts	Volts: 240V	
PYG15WBC	appliance	15W	Cap: BC	Finish: Clear
PYG15WSBC	appliance	15W	Cap: SBC	Finish: Clear
PYG15WSES	appliance	15W	Cap: SES	Finish: Clear
PYG15WSESFRG	fridge	15W	Cap: SES	Finish: Clear
PYG25WBC	appliance	25W	Cap: BC	Finish: Clear
PYG25WSBC	appliance	25W	Cap: SBC	Finish: Clear
PYG25WSES	appliance	25W	Cap: SES	Finish: Clear
PYG40WSESCH	cooker hood	40W	Cap: SES	Finish: Clear
PYG40WSESOV	oven	40W	Cap: SES	Finish: Clear

- For use in a wide range of domestic applications such as cooker hoods, refrigerators and sewing machines.
- Highly reliable and compact in size

Striplights



Code	Watts	Volts			
STRP30WCL221	30W	240V	Length (mm): 221	Cap: S15S	Finish: Clear
STRP30WOP221	30W	240V	Length (mm): 221	Cap: S15S	Finish: Opal
STRP30WCL284	30W	240V	Length (mm): 284	Cap: S15S	Finish: Clear
STRP30WOP284	30W	240V	Length (mm): 284	Cap: S15S	Finish: Opal
STRP60WCL221	60W	240V	Length (mm): 221	Cap: S15S	Finish: Clear
STRP60WOP221	60W	240V	Length (mm): 221	Cap: S15S	Finish: Opal
STRP60WCL284	60W	240V	Length (mm): 284	Cap: S15S	Finish: Clear
STRP60WOP284	60W	240V	Length (mm): 284	Cap: S15S	Finish: Opal

• For use with strip lights and shaver lights

PAR 38



Code	Watts	Volts
PAR38FI 120WES	120	240\/

Cap: ES Beam: Flood

Reflectors



Code	Watts	Volts	
R3930WSES	30W	240V	Cap: R39 - SES
R6340WES	40W	240V	Cap: R63 - ES
R5040WSES	40W	240V	Cap: R50 - SES
R8060WES	60W	240V	Cap: R80 - ES
R6360WES	60W	240V	Cap: R63 - ES
R80100WES	100W	240V	Cap: R80 - ES

- Spotlight reflectors direct a beam of light to the desired areas
- · Ideal for display lighting

Light | Lamps range Halogen



Halogen capsule



Code	Watts	Volts			
Low voltage halogen cap	Low voltage halogen capsules				
HC5WG4	5W	12V	Cap: G4		
HC10WG4	10W	12V	Cap: G4		
HC20WG4	20W	12V	Cap: G4		
HC50WM32	50W	12V	Cap: G6.35		
GGLLL10W	10W	12V	Cap: Wedge		
Mains halogen capsules					
HC25WCLG9	25W	240V	Cap: G9	Finish: Clear	
HC25WFRG9	25W	240V	Cap: G9	Finish: Frosted	
HC40WCLG9	40W	240V	Cap: G9	Finish: Clear	
HC40WFRG9	40W	240V	Cap: G9	Finish: Frosted	
HC60WCLG9	60W	240V	Cap: G9	Finish: Clear	
HC60WFRG9	60W	240V	Cap: G9	Finish: Frosted	

 Halogen capsules suitable for interior display use including shop windows and restaurants

Mains aluminised halogen





Code	Watts	Volts		
HD20WGU10	20W	240V	Cap: GU10	Beam: 36°
HD35WGU10	35W	240V	Cap: GU10	Beam: 36°
HD50WGU10	50W	240V	Cap: GU10	Beam: 36°
HPAR1640WSES	40W	240V	Cap: PAR16	Beam: 30°
HPAR1650WSES	50W	240V	Cap: PAR16	Beam: 36°

- Providing crisp clean light for use in downlighters and uplighters
- Suitable for dimming
- Does not require transformer

Low voltage dichroic halogen and aluminised



Code	Watts	Volts		
Dichroic				
HD20WM252	20W	12V	Cap: MR11 - GU4	Beam: 12°
HD20WM251	20W	12V	Cap: MR11 - GU4	Beam: 24°
HD20WM262	20W	12V	Cap: MR11 - GU4	Beam: 38°
HD20WM268	20W	12V	Cap: MR16 - GU5.3	Beam: 12°
HD20WM294	20W	12V	Cap: MR16 - GU5.3	Beam: 24°
HD20WM269	20W	12V	Cap: MR16 - GU5.3	Beam: 38°
HD20WM2692	20W	12V	Cap: MR16 - GU5.3	Beam: 38°
HD35WM265	35W	12V	Cap: MR11 - GU4	Beam: 12°
HD35WM266	35W	12V	Cap: MR11 - GU4	Beam: 24°
HD35WM299	35W	12V	Cap: MR11 - GU4	Beam: 38°
HD35WM271	35W	12V	Cap: MR16 - GU5.3	Beam: 12°
HD35WM270	35W	12V	Cap: MR16 - GU5.3	Beam: 24°
HD35WM281	35W	12V	Cap: MR16 - GU5.3	Beam: 38°
HD50WM249	50W	12V	Cap: MR16 - GU5.3	Beam: 12°
HD50WM250	50W	12V	Cap: MR16 - GU5.3	Beam: 24°
HD50WM258	50W	12V	Cap: MR16 - GU5.3	Beam: 38°
HD50WM2582	50W	12V	Cap: MR16 - GU5.3	Beam: 38°
GGLLL10MR11	10W	12V	Cap: MR11 - GU4	
Aluminised				
HD50WM2582A	50W	12V	Cap: MR16 - GU5.3	Beam 38°

GU4: Average rated life 3500 hours

GU5.3: Average rated life 4000 hours

M2692 & M2582: Average rated life 2000 hours

- Suitable for display lighting
- Suitable for dimming

Light | Lamps range Halogen



Mains JTT halogen



Code	Watts	Volts	
HJTT60WCLBC	60W	240V	Cap: BC
HJTT60WCLES	60W	240V	Cap: ES

- Cap: ES Finish: Clear

 Can directly replace standard lamps
- providing crisp clean white light

 Suitable for domestic and commercial

Finish: Clear

interior use

Mains linear tugsten halogen



Code	Watts	Volts		
HL100W	100W	240V	Cap: R7s	Length: 78mm
HL150W78	150W	240V	Cap: R7s	Length: 78mm
HL150W118	150W	240V	Cap: R7s	Length: 118mm
HL200W	200W	240V	Cap: R7s	Length: 118mm
HL300W	300W	240V	Cap: R7s	Length: 118mm
HL310W	300W	110V	Cap: R7s	Length: 118mm
HL500W	500W	240V	Cap: R7s	Length: 118mm
HL510W	510W	110V	Cap: R7s	Length: 118mm
HL750W	750W	240V	Cap: R7s	Length: 189mm
HL1000W	1000W	240V	Cap: R7s	Length: 189mm
HL1010W	1000W	110V	Cap: R7s	Length: 169mm
HL1500W	1500W	240V	Cap: R7s	Length: 254mm

- Suitable for floodlights, up lights and displays where light and colour rendering are important
- Suitable for dimming

Mains halogen



Code	Watts	Volts		
Reflector HR5040WSES HR6360WES HR8060WES	40W 60W 60W	240V 240V 240V	Cap: R50 - Cap: R63 - Cap: R80 -	ES
Candle HCNDL60WCLBC HCNDL60WCLES	60W 60W	240V 240V	Cap: BC Cap: ES	Fin Fin

Cap: ES Finish: Clear

• Mains halogen can be used to directly replace standard lamps

Finish: Clear



Light | Lamps range Low energy



Energy saving



Code	Watts	Equivalent GLS	Volts	
CFL9W827BC	9W	40W	240V	Cap: BC
CFL9W827ES	9W	40W	240V	Cap: ES
CFL11W827BC	11W	60W	240V	Cap: BC
CFL11W827ES	11W	60W	240V	Cap: ES
CFL15W827BC	15W	75W	240V	Cap: BC
CFL15W827ES	15W	75W	240V	Cap: ES
CFL20W827BC	20W	100W	240V	Cap: BC
CFL20W827ES	20W	100W	240V	Cap: ES

Size: Standard



Colour temperature: 827 Warm white 2700K

- Average rated life 8000 hours
- Energy saving lamps are not suitable for dimming and should not be used with dimmers, electronic switches or timers as this can shorten the product life.
- Ideal for applications where the lamp is on for long periods
- High quality manufactured lamp type to suit a variety of luminaires

Tubular compact double D 2 pin



Code	Watts	Volts		Colour temperature:	
CFLDD16W8272P	16W	240V	Cap: GR8	827 Warm white 2700K	
CFLDD16W8352P	16W	240V	Cap: GR8	835 White 3500K	
CFLDD28W8272P	28W	240V	Cap: GR8	827 Warm white 2700K	
CFLDD28W8352P	28W	240V	Cap: GR8	835 White 3500K	

Average rated life 8000 hoursNot suitable for dimming



Tubular compact double D 4 pin

Code	Watts	Volts		Colour temperature:
CFLDD16W8274P	16W	240V	Cap: GR10	827 Warm white 2700K
CFLDD16W8354P	16W	240V	Cap: GR10	835 White 3500K
CFLDD28W8274P	28W	240V	Cap: GR10	827 Warm white 2700K
CFLDD28W8354P	28W	240V	Cap: GR10	835 White 3500K
CFLDD38W8274P	38W	240V	Cap: GR10	827 Warm white 2700K
CFLDD38W8354P	38W	240V	Cap: GR10	835 White 3500K
			·	'

Can be dimmed with suitable control gear

Standard compact fluorescent



Code	Watts	Equivalent GLS	Volts	Сар	Tube	Colour temperature
CFL9W8272P	9W	40W	240V	2 PIN	Dual	827 Warm white 2700K
CFL9W8274P	9W	40W	240V	4 PIN	Quad	827 Warm white 2700K
CFL9W8402P	9W	40W	240V	2 PIN	Dual	840 Cool white 4000K
CFL9W8404P	9W	40W	240V	4 PIN	Quad	840 Cool white 4000K
CFL11W8272P	11W	60W	240V	2 PIN	Dual	827 Warm white 2700K
CFL11W8274P	11W	60W	240V	4 PIN	Quad	827 Warm white 2700K
CFL11W8402P	11W	60W	240V	2 PIN	Dual	840 Cool white 4000K
CFL11W8404P	11W	60W	240V	4 PIN	Quad	840 Cool white 4000K
CFL13W8272P	13W	60W	240V	2 PIN	Quad	827 Warm white 2700K
CFL13W8274P	13W	60W	240V	4 PIN	Quad	827 Warm white 2700K
CFL13W8402P	13W	60W	240V	2 PIN	Quad	840 Cool white 4000K
CFL13W8404P	13W	60W	240V	4 PIN	Quad	840 Cool white 4000K
CFL18W8272P	18W	75W	240V	2 PIN	Quad	827 Warm white 2700K
CFL18W8274P	18W	75W	240V	4 PIN	Quad	827 Warm white 2700K
CFL18W8402P	18W	75W	240V	2 PIN	Quad	840 Cool white 4000K
CFL18W8404P	18W	75W	240V	4 PIN	Quad	840 Cool white 4000K
CFL26W8272P	26W	100W	240V	2 PIN	Quad	827 Warm white 2700K
CFL26W8274P	26W	100W	240V	4 PIN	Quad	827 Warm white 2700K
CFL26W8402P	26W	100W	240V	2 PIN	Quad	840 Cool white 4000K
CFL26W8404P	26W	100W	240V	4 PIN	Quad	840 Cool white 4000K

• Not suitable for dimming



Light | Lamps range

T4, T5 compact fluorescent and low energy pendant set



Replacement lamps



Code	Watts	Volts	Qty		
T4FL6W35	6W	230V	10	Colour: White 35	Length: 11" 275mm
T4FL10W35	10W	230V	10	Colour: White 35	Length: 16" 400mm
T4FL16W35	16W	230V	10	Colour: White 35	Length: 20" 500mm
T4FL20W35	20W	230V	10	Colour: White 35	Length: 25" 625mm
T4FL30W35	30W	230V	10	Colour: White 35	Length: 30" 760mm

• To fit GET mini batten range see page 129

T5 miniature fluorescent tubes



 Suitable for kitchens, task lighting and emergency lighting

Energy saving pendant



Code	Description	Qty
GESPEND613	13W Energy saving pendant with 6" flex	: 1

GESPEND618 18W Energy saving pendant 1 with 6" flex

Complies with Part L of the building regulations. Build properties must have a fixed proportion of lighting points suitable for compact fluorescent lamps only.

Requires 1 x 13W 4 pin compact fluorescent lamp (not supplied)

(lamp codes: CFL13W8274P/CFL13W8404P) or

1 x 18W 4 pin compact fluorescent lamp (not supplied)

(lamp codes: CFL18W8274P/CFL18W8404P)



