



RZ3A1A30S2

Connection Type		Klemensli
Operational Voltage		10-30VDC
Product		Electronic Relay
Control		Analog
Type		Time
Contact		PNP
Mechanical Life	Min Qty	10000000
Electrical Life	Min Qty	100000
Operating Temperature		-25 / +70 °C
Time Interval		0,1-30sec
Serial		RZ3 Series
Specifications		Compact design
		Fast and silent switching
		Long life
		Fingerproof design

