



'I' Bar GSM PATCH Antenna

- Miniature Quad Band Patch Antenna
- 824-960MHz
- 1710-1990 MHz
- 1900 -2200 MHz
- Active gain: +3dBi
- 3m RG174 Connecting Lead
- 3M adhesive sticker on Rear
- Ground plane Independent
- Alternative Connectors:
FME / TNC / SMA / MMCX



Applications

- Embedded GSM
- Space Saving Applications
- Car Window

Description

A compact PCB Antenna for GSM Cellular applications where high performance is required from a small size. Using the ANT-GSMQB will give optimum range and reliability to your application.

Part Numbers

	Length	Width	Max Height	Cable Length	Connector
ANT-IBARQB-SMA	116mm	22mm	4mm	3m	SMA (M)

RF Solutions Ltd.,
Unit 21, Cliffe Industrial Estate,
Lewes, E. Sussex. BN8 6JL. England.

Email : sales@rfsolutions.co.uk <http://www.rfsolutions.co.uk>

Tel: +44 (0)1273 898 000 Fax: +44 (0)1273 480 661

