


Electronic Test:


1. 100% test (open, short, miss wire)
2. Contact resistance: 2Ω max.
3. Insulation resistance: 10M Ω min.
4. Hi-pot: 300V DC/10ms.



Conn.1 USB A Female Molding

Conn.2 USB A Male Molding

Pin Assignment



No.	P/N	Description	Qty	Unit
1	61-04102	USB 2.0 cable 28AWG*1P+24AWG*2C+AL/MY+DW+BD Jacket colour PMS:3U2X(black) OD=4.4±0.15mm	5	M
2	R79-04166	USB A Male solder type insulation: white pin gold 5u"	1	SET
3	R79-04148	USB A Female solder type insulation: white pin gold 5u"	1	SET
4	R90-45006	Outer mold: 45P PVC colour: 3U2X(black)	12/1k	KG
5	R91-01001	Inner mold: PE	5/1k	KG
6	R87-04003	Copper foil W=2.5cm	4/100	PCS