



- ErP¹, CEC² and EISA³ Compliant Models
- Wide Range AC Input
- Medical Certifications

Key Market Segments & Applications

Medical, Industrial Computing,
Life Sciences / Laboratory

DTM65-C Series

40W to 65W Medical AC-DC External Power Supplies

DTM65-C Features and Benefits

Features

- CEC and EISA Compliant
- Wide Range AC Input
- 87% Average Efficiency

Benefits

- Easier system compliance
- Global Operation
- Consumes less energy


Specifications

ITEMS		DTM65-C
Input Voltage range		90 - 264VAC (47 - 63Hz)
Inrush Current	A	100A at 230VAC input, 25°C ambient cold start
Input Current	A	2A at 90VAC, Full Load
Power Factor		None
Leakage Current (264VAC 63Hz)	mA	<300uA
Hold Up Time (Typ)	ms	16ms at 230VAC input
Temperature Coefficient		±0.05%/°C
Voltage Accuracy	%	±1%
Adjustment Range		None
Minimum Load	A	None
Total Regulation		12V Model: ±5%, >15V models ±3%
Ripple & Noise	%	1% or 100mV whichever is the greater
Short Circuit Protection	-	Continuous - hiccup mode
Overvoltage Protection	V	110 - 150% of nominal (Cycle input power to reset)
Average Efficiency	%	87%
Operating Temperature	°C	0 to +50°C
Storage Temperature	°C	-10 to +70°C
Humidity (non condensing)		10 - 90% RH
Cooling	-	Convection
Withstand Voltage		Input to Ground 1.5kVAC, Input to Output 4kVAC (Output is connected to Ground)
Vibration (non operating)		23.52m/s ² (10 - 55Hz: constant sweep 1 min X, Y, Z for 1 hour)
Shock		< 196.1 m/s ² (20G)
Safety Agency Approvals	-	CE, UL60601-1, EN60601-1, IEC60601-1
Safety Class	-	Class I
Altitude	m	3000m
Offload Power Consumption	W	< 0.5W
Conducted & Radiated EMI		EN60601-1-2, FCC Part 18 Class B
Immunity		EN55011
Weight (Typ)	g	460g
Size (WxLxH)	mm	69 x 132 x 39.9
Cable Length	mm	1050mm
AC Input Connector		IEC 320-C14 (Accepts IEC 320-C13)
Output Connector		Kycon KPPx-4P or equivalent, Pins 1 & 2: -Vout, Pins 3 & 4: +Vout
Warranty	yrs	2

Notes: (1) ErP - Energy Related Products (2) Californian Energy Commission (3) EISA - Energy Independence and Security Act of 2007


Model Selector						
Model	Output (V)	Maximum Output (A)	Maximum Power (W)	ErP	CEC	EISA Efficiency Level
DTM65PW120C	12	5.0	60	Step 2	V	V
DTM65PW150C	15	4.0	60	Step 2	V	V
DTM65PW180C	18	3.6	65	Step 2	V	V
DTM65PW240C	24	2.7	65	Step 2	V	V
DTM65PW360C	36	1.8	65	Step 2	V	V
DTM65PW480C	48	1.35	65	Step 2	V	V

Outline Drawing DTM65-C Series



Other External AC-DC Products - DTM110-C

DTM65-C Output Connector



Pinout DTM65-C Model

Pin	Function
1	- Vout
2	- Vout
3	+ Vout
4	+ Vout

Alternative output connectors are available
Please contact Sales for further information (min quantities apply)

TDK-LAMBDA EMEA

www.emea.tdk-lambda.com



TDK-Lambda France SAS

Route de Grivery
ZAC des Delaches
CS 41077
91978 Courtaboeuf Cedex
France
Tel: +33 1 60 12 71 65
Fax: +33 1 60 12 71 66
france@fr.tdk-lambda.com
www.fr.tdk-lambda.com



Italy Sales Office
Via dei Lavoratori 128/130
20092 Cinisello Balsamo (MI)
Italy
Tel: +39 02 61 29 38 63
Fax: +39 02 61 29 09 00
info.italia@it.tdk-lambda.com
www.it.tdk-lambda.com



TDK-Lambda Germany GmbH

Karl-Bold-Strasse 40
77855 Achern
Germany
Tel: +49 7841 666 0
Fax: +49 7841 5000
info.germany@de.tdk-lambda.com
www.de.tdk-lambda.com



Austria Sales Office
Aredstrasse 22
2544 Leobersdorf
Austria
Tel: +43 2256 655 84
Fax: +43 2256 645 12
info.germany@de.tdk-lambda.com
www.de.tdk-lambda.com



TDK-Lambda UK Ltd.

Kingsley Avenue
Ilfracombe
Devon EX34 8ES
United Kingdom
Tel: +44 (0) 12 71 85 66 66
Fax: +44 (0) 12 71 86 48 94
powersolutions@uk.tdk-lambda.com
www.uk.tdk-lambda.com



TDK-Lambda Israel

Kibbutz
Givat Hashlosha 48800
Israel
Tel: +9 723 902 4333
Fax: +9 723 902 4777
info@nemic.co.il
www.tdk-lambda.co.il



Russia

Technical Support:
St Petersburg
Tel: +7 (812) 6580463
Sales:
Moscow
Tel: +7 (499) 7557732
info@tdk-lambda.ru
www.tdk-lambda.ru

LOCAL DISTRIBUTION

