



ESKA Fuses

Product Dimensions(mm)

Part Number	A	B	C	D	E	F	Lead
	Max.	Max.	Typ.	Min.	Max.	Typ.	Size(φ)
LP16-300	7.8	11.7	5.1	7.6	3.0	1.2	0.8
LP16-400	9.6	13.8	5.1	7.6	3.0	1.2	0.8
LP16-500	11.1	13.9	5.1	7.6	3.0	1.2	0.8
LP16-600	11.4	16.8	5.1	7.6	3.0	1.2	0.8
LP16-700	11.9	19.7	5.1	7.6	3.0	1.2	0.8
LP16-800	13.4	21.2	5.1	7.6	3.0	1.2	0.8
LP16-900	14.7	21.4	5.1	7.6	3.0	1.2	0.8
LP16-1000	17.2	24.8	5.1	7.6	3.0	1.2	0.8
LP16-1100	18.2	26.7	5.1	7.6	3.0	1.2	0.8
LP16-1200	18.2	28.5	10.2	7.6	3.6	1.4	1.0
LP16-1400	28.6	28.7	10.2	7.6	3.4	1.4	1.0



Part Marking System



※Lead materials:Tin-plate metal wire.

※Lead-free devices are available.

Electrical Characteristics

Part Number	I_H (A)	I_T (A)	T_{trip} (S)	V_{max} (V)	I_{max} (A)	Pd_{typ} (W)	R_{min} (Ω)	R_{Tmax} (Ω)
LP16-300	3.0	5.1	2.0	16	100	2.3	0.034	0.105
LP16-400	4.0	6.8	3.5	16	100	2.4	0.020	0.063
LP16-500	5.0	8.5	3.6	16	100	2.6	0.014	0.044
LP16-600	6.0	10.2	5.8	16	100	2.8	0.009	0.030
LP16-700	7.0	11.9	8.0	16	100	3.0	0.006	0.021
LP16-800	8.0	13.6	9.0	16	100	3.0	0.005	0.018
LP16-900	9.0	15.3	12.0	16	100	3.3	0.004	0.015
LP16-1000	10.0	17.0	12.5	16	100	3.3	0.003	0.012
LP16-1100	11.0	18.7	13.5	16	100	3.7	0.003	0.010
LP16-1200	12.0	20.4	16.0	16	100	4.2	0.002	0.009
LP16-1400	14.0	23.8	20.0	16	100	4.6	0.002	0.008