


Copper Foil Tape

Model	Length (M)	Width (mm)
CFT-25/10M	10	25mm
CFT-50/10M	10	50mm
CFT-25/20M	20	25mm
CFT-50/20M	20	50mm



Specification

Backing : Copper
Adhesive : Non Conductive Acrylic
Backing thickness : 0.018 ± 0.005 mm
Adhesive thickness : 0.032 ± 0.005 mm
Total thickness : 0.05 ± 0.01 mm
Color : Copper

Technical Data

Electrical Resistance : $0.03 \sim 0.05$ ohm
Adhesive power : 1.5kg/25mm
Tensile strength : 4.5kg/25mm
Elongate Rate : $>5\%$
Operating temperature : $0^{\circ}\text{C} \sim 100^{\circ}\text{C}$