

ETL Extension test leads



- **30m and 50m versions**
- **Suitable for direct R1 measurements**
- **Easy re-wind of cable with Tangle-free cable guide**
- **Compact and light design**
- **BS EN61010 CAT IV 600 V**

DESCRIPTION

The Megger ETL30 and ETL50 Extension Test Leads are convenient and compact long test leads, designed for direct continuity measurement of R2 values.

When working on a dead system, disconnect equipotential bonding to eliminate parallel paths and connect one end of the lead to the main Earth terminal at the distribution board. Connect the other end of the lead to your continuity tester, and probe around the circuit CPC points checking for continuity, and direct R2 measurements

This compact 30m or 50m extension test lead eliminates the need for crossover connections for R1 + R2 measurements by providing a single R2 value. The furthest point in the circuit can be easily verified, and every earth point on the circuit checked for integrity prior to energising.

Ideal for use on lighting circuits to check switches and roses where R1 + R2 is not possible, and on multi-light arrays (e.g. commercial and retail premises) to ensure every fitting is earthed with minimal disassembly.

The ETL30 and ETL50 are also useful for general fault-finding on new and in-use circuits where a loop break may be present or an open circuit fault exists at some distance

from the distribution board.

The small and light design is easy to carry and use. The outer frame is convenient to hold, with the low-friction drum preventing over-run for tangle-free extension, combined with a cable tensioning brush for easy rewind.

SPECIFICATION

Voltage 0 V to 600 V dc/ac (0/1kHz)

Operating Temperature -10°C to +50°C

Safety rating
IEC/EN61010-1:2001-02 over voltage Cat IV 600 V

Dimensions
176mm x 26mm

Weight
1Kg

Warranty
1 year

ORDERING INFORMATION

Item (Qty)	Order Code
ETL30 Extension Test Lead 30m	1000-215
ETL50 Extension Test Lead 50m	1000-217

UK
Archcliffe Road Dover
CT17 9EN England
T +44 (0) 1304 502101
F +44 (0) 1304 207342
E uksales@megger.com

UNITED STATES
4271 Bronze Way
Dallas TX 75237-1088 USA
T 800 723 2861 (USA only)
T +1 214 333 3201
F +1 214 331 7399

OTHER TECHNICAL SALES OFFICES
Norrilstown USA, Sydney AUSTRALIA,
Toronto CANADA, Trappes FRANCE,
Kingdom of BAHRAIN, Mumbai
INDIA, Johannesburg SOUTH AFRICA
and Conjure THAILAND.

Registered to ISO 9001:2000 Cert no. Q 09290
Registered to ISO 14001-1996 Cert no. EMS 61597

ETL_DS_en_V01

www.megger.com
Megger is a registered trademark