



Magnetic Contact Switches


Specification: MCS-136 Series

- *Metal magnetic contacts
- *Ideal for industrial or commercial use
- *Screws included
- *Standard 18" #22AWG leads
- *2 conductor jacket cable on request (BS-2071J)
- *Armoured cable on request (BS-2071AR)
- *Resistor, diode and supervisory loop available on request
- *Longer leads available



 ϵ

Dimensions (mm)





Order Information

Part Number	Loop Type	Reed Form	Closed Gap Inch (mm)	Departure Gap Inch (mm)	Max Initial Contact Resistance (Ohm)	Max Initial Contact rating (W)	Max Switching Voltage (VDC/VAC)	Max Switching Current (A)
MCS-136-1	Closed	N/O	1.5(38)	1.65 (42)	0.150	7.5	100	0.4
MCS-136-2	Open	N/C	11⁄4(32)		0.150	3	30	0.2
MCS-136-3	Closed & Open	SPDT	11⁄4(32)		0.150	3	30	0.2
MCS-136-4	DPDT	2SPDT	11⁄4(32)		0.150	3	30	0.2



As part of the company policy of continued product improvement, specifications may change without notice. Our sales office will be pleased to help you with the latest information on this product range and the details of our full design and manufacturing service. All products are supplied to our standard conditions of sale unless otherwise agreed in writing.

Phone: +44 (0)1255 862236

www.assemtech.co.uk

Fax: +44 (0)1255 862014