COMUS Group

Magnetic Contact Switches




Specification: MCS-137 Series


*Metal magnetic contacts

*Ideal for securing chain link fence

- *Bracket included
- *2 conductor jacket cable on request (BS-2071J)
- *Weather resistane Aluminum housing *Resistor, diode and supervisory loop available on request
- *Switches and magnets are available separately
- *Longer leads available

Dimensions (mm)





c(UL) US

Order Information

Part Number	Loop Туре	Reed Form	Closed Gap Inch (mm)	Departure Gap Inch (mm)	Max Initial Contact Resistance (Ohm)	Max Initial Contact rating (W)	Max Switching Voltage (VDC/VAC)	Max Switching Current (A)
MCS-137-1	Closed	N/O	2.95(75)	3.18 (80)	0.150	7.5	100	0.4
MCS-137-2	Closed	N/O	3½(90)	3.75 (95)	0.150	7.5	100	0.4
MCS-137-3	Open	N/C	21⁄2(65)		0.150	3	30	0.2
MCS-137-4	Closed & Open	SPDT	21⁄2(65)		0.150	3	30	0.2
MCS-137-5	DPDT	2SPDT	21⁄2(65)		0.150	3	30	0.2



As part of the company policy of continued product improvement, specifications may change without notice. Our sales office will be pleased to help you with the latest information on this product range and the details of our full design and manufacturing service. All products are supplied to our standard conditions of sale unless otherwise agreed in writing.

Phone : +44 (0)1255 862236

www.assemtech.co.uk

©2010 Copyright Assemtech Europe Ltd, Unit 7, Rice Bridge Industrial Estate, Thorpe - Le - Soken, Essex, CO16 0HL, ENGLAND. USA: + 1 973 777 6900 - Belgium: + 32 (0)12 390400 - France: + 33 (0) 1 43 96 86 10