
LABFACILITY TEMPERATURE & PROCESS TECHNOLOGY

Data sheet

Thermocouple Extension & Compensating Cable

ANSI PVC Insulated Flat Pair (ANSI MC96.1)



Туре КХ

Type TX

- PVC insulated flat pair construction •
- Conductors laid flat PVC insulated with overall PVC sheath .
- All round general purpose cable, both waterproof and very flexible
- Thermocouple extension types for K, J, & T •
- Compensating types VX (KCB) for types K Thermocouples
- Stranded conductors available, 7/0.2mm •
- Available in 10, 25, 50, 100 & 200 metre lengths •
- **Tolerance Class 2**
- Insulation rating -10°C to 105°C
- Colour code (cores & jacket) to ANSI MC96.1

T/C Type Extension:	Conductors	Cores	Jacket	Reel Length	Order code
КХ	7/0.2mm	+Yellow/-Red	Yellow	10 metres	XE-2807-010
КХ	7/0.2mm	+Yellow/-Red	Yellow	25 metres	XE-2807-025
КХ	7/0.2mm	+Yellow/-Red	Yellow	50 metres	XE-2807-050
КХ	7/0.2mm	+Yellow/-Red	Yellow	100 metres	XE-2807-100
КХ	7/0.2mm	+Yellow/-Red	Yellow	200 metres	XE-2807-200
JX	7/0.2mm	+ White/-Red	Black	10 metres	XE-2806-010
JX	7/0.2mm	+ White/-Red	Black	25 metres	XE-2806-025
JX	7/0.2mm	+ White/-Red	Black	50 metres	XE-2806-050
JX	7/0.2mm	+ White/-Red	Black	100 metres	XE-2806-100
JX	7/0.2mm	+ White/-Red	Black	200 metres	XE-2806-200



TEMPERATURE & PROCESS TECHNOLOGY

Data sheet

Thermocouple Extension & Compensating Cable

ANSI PVC Insulated Flat Pair (ANSI MC96.1)

TX TX TX TX TX	7/0.2mm 7/0.2mm 7/0.2mm 7/0.2mm 7/0.2mm	+Blue/-Red +Blue/-Red +Blue/-Red +Blue/-Red +Blue/-Red	Blue Blue Blue Blue Blue	10 metres 25 metres 50 metres 100 metres 200 metres	XE-2808-010 XE-2808-025 XE-2808-050 XE-2808-100 XE-2808-200				
Compensating:									
VX (KCB)	7/0.2mm	+Brown/-Red	Red	10 metres	XE-2809-010				
VX (KCB)	7/0.2mm	+Brown/-Red	Red	25 metres	XE-2809-025				
VX (KCB)	7/0.2mm	+Brown/-Red	Red	50 metres	XE-2809-050				
VX (KCB)	7/0.2mm	+Brown/-Red	Red	100 metres	XE-2809-100				
VX (KCB)	7/0.2mm	+Brown/-Red	Red	200 metres	XE-2809-200				

