



Data sheet

Glassfibre Exposed Welded Tip Thermocouples with Plug

Types K with 're-wireable' miniature flat pin plug (ANSI MC96.1)



Type 'K'

- Thermocouple type K
- Fast response, welded exposed junction
- 1, 2, 5 or 10 metre long glassfibre insulated flat pair cable
- Good temperature resistance (not suitable in fluids)
- 1/0.3mm conductors
- 'Re-Wireable' miniature flat pin plug
- Temperature range -60°C to +350°C (short periods up to 400°C)
- Tolerance to ANSI MC96.1 Class 2
- Colour code to ANSI MC96.1
- Ideal for test & development applications

T/C Type	Conductors	Length	Termination	+Positive tail wire	-Negative tail wire code	Order
'K'	1/0.3mm	1 metres	Mini plug (re-wireable)	Yellow	Red	XE-3586-001
'K'	1/0.3mm	2 metres	Mini plug (re-wireable)	Yellow	Red	XE-3588-001
'K'	1/0.3mm	5 metres	Mini plug (re-wireable)	Yellow	Red	XE-3562-001
'K'	1/0.3mm	10 metres	Mini plug (re-wireable)	Yellow	Red	XE-3573-001

