



Double-deck terminal block; Through/through terminal block; N/N;
without marker carrier; blue housing; suitable for Ex i applications

Item No.: 2000-2204



Marking

RoHS ✓
Compliant

Business data

Supplier	WAGO
Item no.	2000-2204
GTIN / EAN	4055143267700
Content	1

Notes



Technical data



Miscellaneous

Ratings per	IEC/EN 60947-7-1
Rated voltage (III / 3) [V]	500 [V]
Rated impulse voltage (III / 3) [kV]	6 [kV]
Rated current [A]	13.5 [A]

Technical data	
Rated current (2) [A]	16 [A]
Legend (ratings)	(III / 3) Overvoltage category III / Pollution degree 3
Type of wiring	Front-entry wiring
Total number of connection points	4
Total number of potentials	2
Number of levels	2
Connection technology	Push-in CAGE CLAMP®
Number of connection points (connection type)	2
Actuation type	Push-in
Connectable conductor materials	Copper
Nominal cross section	1 mm ²
Solid conductor	0.14 ... 1.5 mm ² / 24 ... 16 AWG
Solid conductor, push-in termination	0.5 ... 1.5 mm ² / 20 ... 16 AWG
Fine-stranded conductor	0.14 ... 1.5 mm ² / 24 ... 16 AWG
Fine-stranded conductor with ferrule, push-in termination, f	0.5 mm ² / 20 AWG
Strip length	9 ... 11 mm / 0.35 ... 0.43 Inch
Number of connection points (connection type 2)	2
Width	3.5 mm / 0.138 Inch
Height from upper-edge of DIN-35 rail	51.7 mm / 2.035 Inch
Depth	69.7 mm / 2.744 Inch
Design	horizontal
Type of mounting	Carrier rail 35 x 15
Potential marking	N/N
Marking level	Center/side marking
Color	blue
Insulating material	Polyamide 66 (PA 66)
Fire load [MJ]	0.152 [MJ]
Weight [g]	7.33 [g]
Product Family	TOPJOB® S
Main product function	Multilevel terminal blocks
Product type	Through rail-mount term. blocks

Images & drawings





Address

WAGO Kontakttechnik GmbH & Co. KG

Hansastr. 27

32423 Minden

Telefon: 0571/887-0

Fax: 0571/887-169

<http://www.wago.com>

© WAGO Kontakttechnik GmbH & Co. KG

Technische Änderungen und Irrtümer vorbehalten.