







Part Number: PPS 24 (Alternate Part No: S1325)

**Housed Reed Switch Product Data Sheet** 


## **PICTURE**




- Resistant to Ambient Environmental Conditions
- Hermetically Sealed & Inert Gas Filled
- · Case Material : Polypropylene



## **DIMENSIONS**





Drawings not to scale.
All dimensions in inches (mm) nominal.

SPECIFICATION		
Contact Form / Style		Normally Open
Switching Voltage	Max. VAC	24
Switching Current	Max. A	0.1
Switching Capacity	Max. VA	1.0
Contact Resistance	Max. mΩ	200
Switching Distance	Min. mm	Dependant on magnet
Operating Temperature	Deg °C	-20° to +70°
Storage Temperature	Deg °C	-25° to +70°

As part of the company policy of continued product improvement, specifications may change without notice. Our sales office will be pleased to help you with the latest information on this product range and the details of our full design and manufacturing service. All products are supplied to our standard conditions of sale unless otherwise agreed in writing.

Phone: (1) 973 777 6900

www.comus-intl.com

Fax: (1) 973 777 8405