

### Heavy Duty Thermocouple



- Type J thermocouple
- Stainless steel probe 4.5mm x 150mm
- 2 metres stainless steel overbraided cable 7/0.2mm
- Temperature rating -60°C to +350°C
- Grounded measuring junction

#### Specifications:

Sensor type:	Type J thermocouple to IEC 584
Construction:	Stainless steel probe 4.5mm diameter x 150mm long, junction grounded to sheath at tip
Lead type:	2 metres glassfibre extension cable with stainless steel overbraid, 7/0.2mm conductors
Lead termination:	Bare wire tails
Temperature range:	-60°C to +350°C

Product code	Manufacturer's Part Number	Rapid Part Number
FAA-GSJ-4.5-150-2.0-C4-T	XE-3400-001	61-1266