


TEMPERATURE & PROCESS TECHNOLOGY

Miniature Quick Wire plug

Types K, J, T (IEC Colour Code)






- These quick connect versions allow rapid termination
- Miniature connector with flat plug pins
- Easy 'jab-in' connection for rapid termination, Just push-in wire & tighten screw
- Contacts are polarised to prevent incorrect connection
- Available in Thermocouple types K, J, T
- For Types K, J, T contacts are made from true Thermocouple alloys
- Colour coded in accordance with IEC specification
- Maximum continuous temperature 220 deg°C

T/C Type	Colour Code (IEC)	+Positive Contact (alloy type)	-Negative Contact (alloy type)	Manufacturer's Part Number	Rapid Order Code
K	Green	+Nickel Chromium	-Nickel Alloy	XE-1111-001	61-3005
J	Black	+Iron	-Copper Nickel	XE-1171-001	61-3006
Т	Brown	+Copper	-Copper Nickel	XE-1201-001	61-3007

Schematic Drawing



Quick-Wire Miniature Plug

