

TEMPERATURE & PROCESS TECHNOLOGY

Miniature Quick Wire Panel Mount Socket with Stainless Steel Bracket Rapid

Types K, J, T (IEC Colour Code)



- Miniature size sockets supplied with stainless steel brackets
- Available in Thermocouple types K, J, T
- For Types K, J, T contacts are made from true Thermocouple alloys
- Colour coded in accordance with IEC specification
- Maximum continuous operating temperature 220 deg°C

T/C Type	Colour Code (IEC)	+Positive Contact (alloy type)	-Negative Contact (alloy type)	Manufacturer's Part Number	Rapid Order Code
K	Green	+Nickel Chromium	-Nickel Alloy	XE-1106-001	61-3014
J	Black	+Iron	-Copper Nickel	XE-1166-001	61-3015
Т	Brown	+Copper	-Copper Nickel	XE-1196-001	61-3016

Schematic Drawing



