

### Standard Thermocouple Socket with Stainless Steel mounting bracket

Types K, J, T  
(IEC Colour Code)



- Standard size in-line Thermocouple Socket with stainless steel panel mounting bracket
- Intended for use in more industrial processes but can be used in all applications as desired
- Available in Thermocouple types K, J, T
- For Types K, J, T contacts are made from true Thermocouple alloys
- Colour coded in accordance with IEC specification
- Maximum continuous operating temperature 220 deg°C

T/C Type	Colour Code (IEC)	+Positive Contact (alloy type)	-Negative Contact (alloy type)	Manufacturer's Part Number	Rapid Order Code
K	Green	+Nickel Chromium	-Nickel Alloy	XE-1408-001	<b>61-3034</b>
J	Black	+Iron	-Copper Nickel	XE-1468-001	<b>61-3035</b>
T	Brown	+Copper	-Copper Nickel	XE-1498-001	<b>61-3036</b>

#### Schematic Drawing

