TEMPERATURE & PROCESS TECHNOLOGY

Standard In-Line Thermocouple Sockets

Types K, J, T (ANSI Colour Code)





- Standard sized in-line thermocouple socket with connections to suit thermocouple type being used
- Accepts standard round plug pins
- Suitable for industrial applications
- Available in Thermocouple types K, J, T
- For Types K, J, T contacts are made from true Thermocouple alloys
- Contacts are polarised to prevent incorrect connection
- Colour coded in accordance with ANSI specification
- Maximum continuous operating temperature 220 deg°C

Т/С Туре	Colour Code (ANSI)	+Positive Contact (alloy type)	-Negative Contact (alloy type)	Manufacturer's Part Number	Rapid Order Code
К	Yellow	+Nickel Chromium	-Nickel Alloy	XE-1432-001	61-3073
J	Black	+lron	-Copper Nickel	XE-9132-001	61-3074
Т	Blue	+Copper	-Copper Nickel	XE-1522-001	61-3075

Schematic Drawing

