

Standard Quick Wire Panel Mounting Socket with Stainless Steel Bracket

Types K, J, T
(ANSI Colour Code)



- Standard size sockets supplied with stainless steel brackets
- Easy 'jab-in' connection for rapid termination, just push wire in and tighten screw
- Intended for use in more industrial processes but can be used in all applications as desired
- Available in Thermocouple types K, J, T
- For Types K, J, T contacts are made from true Thermocouple alloys
- Colour coded in accordance with ANSI specification
- Maximum continuous operating temperature 220 deg°C

T/C Type	Colour Code (ANSI)	+Positive Contact (alloy type)	-Negative Contact (alloy type)	Manufacturer's Part Number	Rapid Order Code
K	Yellow	+Nickel Chromium	-Nickel Alloy	XE-1439-001	61-3088
J	Black	+Iron	-Copper Nickel	XE-9139-001	61-3089
T	Blue	+Copper	-Copper Nickel	XE-1529-001	61-3090