

Connector Panels – for Panel Mounting Thermocouple Sockets



Miniature Panel:



suitable with Miniature Panel Sockets (not included):



Standard Panel:



suitable with Standard Panel Sockets (not included):



- Anodised Aluminium Faceplates
- Suitable for miniature & standard fascia panel mounting thermocouple sockets
- Etch matt & satin anodised finish
- 1 to 12 way panels in single row (as shown)
- 16, 20 & 24 way panels are in two rows i.e. 16 way = 2 rows of eight, 20 way = 2 rows of 10, 24 way = 2 rows of 12
- Both miniature & standard panels have 4 x 3.2mm fixing holes, positioned 5mm centre line from corners edges

Connector Panels – for Panel Mounting Thermocouple Sockets



Miniature

Panel Size	No. of rows/holes	Width	Height	Thickness	Manufacturer's Part Number	Rapid Part Number
1 way	1 x 1	40mm	45mm	2mm	XE-1701-001	61-3097
2 way	1 x 2	55mm	45mm	2mm	XE-1702-001	61-3098
3 way	1 x 3	70mm	45mm	2mm	XE-1703-001	61-3099
4 way	1 x 4	85mm	45mm	2mm	XE-1704-001	61-3100
5 way	1 x 5	100mm	45mm	2mm	XE-1705-001	61-3101
6 way	1 x 6	115mm	45mm	2mm	XE-1706-001	61-3102
8 way	1 x 8	145mm	45mm	2mm	XE-1707-001	61-3103
10 way	1 x 10	175mm	45mm	2mm	XE-1708-001	61-3104
12 way	1 x 12	205mm	45mm	2mm	XE-1709-001	61-3105
16 way	2 x 8	145mm	75mm	2mm	XE-1710-001	61-3106
18 way	2 x 9	160mm	75mm	2mm	XE-1711-001	61-3107
20 way	2 x 10	175mm	75mm	2mm	XE-1712-001	61-3108
24 way	2 x 12	205mm	75mm	2mm	XE-1713-001	61-3109

Standard

Panel Size	No. of rows/holes	Width	Height	Thickness	Manufacturer's Part Number	Rapid Part Number
1 way	1 x 1	50mm	66mm	2.5mm	XE-1801-001	61-3110
2 way	1 x 2	69mm	66mm	2.5mm	XE-1802-001	61-3111
3 way	1 x 3	88mm	66mm	2.5mm	XE-1803-001	61-3112
4 way	1 x 4	107mm	66mm	2.5mm	XE-1804-001	61-3113
5 way	1 x 5	126mm	66mm	2.5mm	XE-1805-001	61-3114
6 way	1 x 6	145mm	66mm	2.5mm	XE-1806-001	61-3115
8 way	1 x 8	183mm	66mm	2.5mm	XE-1807-001	61-3116
10 way	1 x 10	221mm	66mm	2.5mm	XE-1808-001	61-3117
12 way	1 x 12	259mm	66mm	2.5mm	XE-1809-001	61-3118
16 way	2 x 8	183mm	111mm	2.5mm	XE-1810-001	61-3119
18 way	2 x 9	202mm	111mm	2.5mm	XE-1811-001	61-3120
20 way	2 x 10	221mm	111mm	2.5mm	XE-1812-001	61-3121
24 way	2 x 12	259mm	111mm	2.5mm	XE-1813-001	61-3122