

Button Magnet Thermocouple, Type K

1 metre Teflon[®] insulated cable with type K miniature plug



- Button magnet thermocouple
- Ideal for ferrous metal surface measurement
- Spring loaded junction to ensure good contact
- 1 metre long Teflon[®] insulated twin-twisted wires
- Fitted miniature plug (200°C)
- Sensor range to 250°C

Specifications

Sensor type:	Type K thermocouple to IEC 584
Construction:	Thermo-element located in 1/2" diameter magnet
Cable/Termination:	1 metre PFA Teflon [®] insulated with miniature plug termination
Thermocouple junction:	Grounded at tip
Magnet:	1/2" diameter button type
Temperature range:	-50°C to + 250°C

Product code	Manufacturer's Part Number	Rapid Order Number
BMS-K-1-C70-MP	XE-3460-001	61-3186

Fitted miniature plug dimensions

